

FBSRH 3-8 - Short-circuit connector



3033803

<https://www.phoenixcontact.com/us/products/3033803>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Short-circuit connector, pitch: 8.2 mm, number of positions: 3, nominal current: 32 A, color: red



Your advantages

- The bridge has a molded extraction tool which means that it can be used conveniently and without tools for individual bridging tasks

Commercial data

Item number	3033803
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE29
Product key	BE2Z2X
GTIN	4046356666923
Weight per piece (including packing)	4.252 g
Weight per piece (excluding packing)	3.752 g
Customs tariff number	85366990
Country of origin	CN

FBSRH 3-8 - Short-circuit connector



3033803

<https://www.phoenixcontact.com/us/products/3033803>

Technical data

Product properties

Product type	Short-circuit connector
Number of positions	3
Pitch	8.2 mm

Electrical properties

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Connection data

Maximum load current	32 A (The current values for the jumpers can deviate when used in different modular terminal blocks. The precise values can be found in the accessories data for the respective modular terminal blocks.)
----------------------	---

Dimensions

Width	22.9 mm
Height	40.3 mm
Depth	40.3 mm
Pitch	8.2 mm

Material specifications

Color	red (RAL 3001)
Material	Copper
Flammability rating according to UL 94	V0
Insulating material	PA

Mounting

Mounting type	Plug-in mounting
---------------	------------------

Drawings

Schematic diagram



FBSRH 3-8 - Short-circuit connector



3033803

<https://www.phoenixcontact.com/us/products/3033803>

Classifications

ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

ETIM

ETIM 10.0	EC000489
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBSRH 3-8 - Short-circuit connector



3033803

<https://www.phoenixcontact.com/us/products/3033803>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com