

STG 4-VBST 4 - Connector housing



3070419

<https://www.phoenixcontact.com/us/products/3070419>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Connector housing, depth: 45 mm, width: 24.4 mm, height: 15.7 mm, number of positions: 4, color: black

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3070419 |
| Packing unit | 1,500 pc |
| Minimum order quantity | 1,500 pc |
| Sales key | BE29 |
| Product key | BE5Z3X |
| GTIN | 4046356559553 |
| Weight per piece (including packing) | 4.1 g |
| Weight per piece (excluding packing) | 4.1 g |
| Customs tariff number | 85389099 |
| Country of origin | DE |

STG 4-VBST 4 - Connector housing



3070419

<https://www.phoenixcontact.com/us/products/3070419>

Technical data

Product properties

| | |
|---------------------|-------------------|
| Product type | Mounting material |
| Number of positions | 4 |

Dimensions

| | |
|--------|---------|
| Width | 24.4 mm |
| Height | 15.7 mm |
| Depth | 45 mm |

Material specifications

| | |
|--|------------------|
| Color | black (RAL 9005) |
| Material | PA |
| Flammability rating according to UL 94 | V0 |

STG 4-VBST 4 - Connector housing



3070419

<https://www.phoenixcontact.com/us/products/3070419>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27440202 |
| ECLASS-15.0 | 27440202 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC000437 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31261500 |
|-------------|----------|

STG 4-VBST 4 - Connector housing



3070419

<https://www.phoenixcontact.com/us/products/3070419>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|--------------|
| CO2e kg | 0.03 kg CO2e |
|---------|--------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com