

ESB 2-FK - Insertion bridge



3131138

<https://www.phoenixcontact.com/us/products/3131138>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insertion bridge, pitch: 6.15 mm, number of positions: 2, length: 10 mm, color: gray



Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 3131138 |
| Packing unit | 10 pc |
| Minimum order quantity | 10 pc |
| Note | Made to order (non-returnable) |
| Sales key | BE19 |
| Product key | BE1Z2X |
| GTIN | 4017918093006 |
| Weight per piece (including packing) | 1.49 g |
| Weight per piece (excluding packing) | 1.38 g |
| Customs tariff number | 85366990 |
| Country of origin | PL |

ESB 2-FK - Insertion bridge

3131138

<https://www.phoenixcontact.com/us/products/3131138>



Technical data

Product properties

| | |
|---------------------|------------------|
| Product type | Insertion bridge |
| Number of positions | 2 |
| Pitch | 6.15 mm |

Dimensions

| | |
|--------|---------|
| Width | 3 mm |
| Height | 24 mm |
| Length | 10.2 mm |
| Pitch | 6.15 mm |

Material specifications

| | |
|--|----------|
| Color | gray |
| Material | PA 66 V2 |
| Flammability rating according to UL 94 | PA66 V2 |

ESB 2-FK - Insertion bridge

3131138

<https://www.phoenixcontact.com/us/products/3131138>



Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

ESB 2-FK - Insertion bridge



3131138

<https://www.phoenixcontact.com/us/products/3131138>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com