

# UPZ/ 2 - Strain relief

3045554

<https://www.phoenixcontact.com/us/products/3045554>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Strain relief, width: 9.3 mm, height: 36.7 mm, number of positions: 2, color: black

## Your advantages

- The conductor can be fixed using Phoenix Contact cable binders
- Strain relief can be snapped onto the outside of the plug as an option

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 3045554       |
| Packing unit                         | 50 pc         |
| Minimum order quantity               | 50 pc         |
| Sales key                            | BE01          |
| Product key                          | BE114Z        |
| GTIN                                 | 4046356055758 |
| Weight per piece (including packing) | 0.897 g       |
| Weight per piece (excluding packing) | 0.897 g       |
| Customs tariff number                | 39269097      |
| Country of origin                    | PL            |

# UPZ/ 2 - Strain relief

3045554

<https://www.phoenixcontact.com/us/products/3045554>



## Technical data

### Product properties

|                     |                   |
|---------------------|-------------------|
| Product type        | Mounting material |
| Number of positions | 2                 |

### Dimensions

|        |         |
|--------|---------|
| Width  | 9.3 mm  |
| Height | 36.7 mm |

### Material specifications

|  |                  |
|--|------------------|
| Color                                  | black (RAL 9005) |
| Material                               | PA-GF            |
| Flammability rating according to UL 94 | V0               |

# UPZ/ 2 - Strain relief



3045554

<https://www.phoenixcontact.com/us/products/3045554>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3045554>



**EAC**

Approval ID: KZ7500651131219505

# UPZ/ 2 - Strain relief



3045554

<https://www.phoenixcontact.com/us/products/3045554>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-15.0 | 27250190 |
| ECLASS-13.0 | 27141190 |

### ETIM

|           |          |
|-----------|----------|
| ETIM 10.0 | EC002848 |
|-----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

# UPZ/ 2 - Strain relief



3045554

<https://www.phoenixcontact.com/us/products/3045554>

## Environmental product compliance

### EU RoHS

|   |                    |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

### China RoHS

|  |  |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E                                   |
|  | No hazardous substances above the limits |

### EU REACH SVHC

|                                     |                            |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

### EF3.1 Climate Change

|         |           |
|---------|-----------|
| CO2e kg | 0 kg CO2e |
|---------|-----------|

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)