

# KZMP-RV 8:1-8 - Pair of marking masks



3191330

<https://www.phoenixcontact.com/us/products/3191330>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Pair of marking masks, Card, labeled, horizontal: Consecutive numbers, mounting type: adhesive, for terminal block width: 7.62 mm, Number of individual labels: 20



## Commercial data

Item number	3191330
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BE19
Product key	BE1ZWX
GTIN	4017918093495
Weight per piece (including packing)	12.17 g
Weight per piece (excluding packing)	12.17 g
Customs tariff number	39269097
Country of origin	CH

# KZMP-RV 8:1-8 - Pair of marking masks



3191330

<https://www.phoenixcontact.com/us/products/3191330>

## Technical data

### Product properties

Product type	Labeled terminal marker
Pitch	7.62 mm

### Marking

Number of individual labels	20
Number of individual labels per row	1
Printing direction	horizontal
Printing	Consecutive numbers

### Mounting

Mounting type	adhesive
---------------	----------

### Material specifications

Color	white
-------	-------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Dimensions

Width	65 mm
Pitch	7.62 mm
Length	7.61 mm

# KZMP-RV 8:1-8 - Pair of marking masks



3191330

<https://www.phoenixcontact.com/us/products/3191330>

## Classifications

### UNSPSC

UNSPSC 21.0	39121410
-------------	----------

# KZMP-RV 8:1-8 - Pair of marking masks



3191330

<https://www.phoenixcontact.com/us/products/3191330>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)