

D-DT 2,5-QUATTRO-MT - End cover



3054419

<https://www.phoenixcontact.com/us/products/3054419>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, width: 2.2 mm, height: 29.1 mm, color: gray



Commercial data

Item number	3054419
Packing unit	50 pc
Minimum order quantity	1 pc
Product key	BE2Z1X
GTIN	4046356144179
Weight per piece (including packing)	3.63 g
Weight per piece (excluding packing)	3.5 g
Country of origin	PL

D-DT 2,5-QUATTRO-MT - End cover



3054419

<https://www.phoenixcontact.com/us/products/3054419>

Technical data

Product properties

Product type	End cover
--------------	-----------

Material specifications

Color	gray
Material	PA
Flammability rating according to UL 94	V0
Static insulating material application in cold	-60 °C
Temperature index of insulation material (DIN EN 60216-1 (VDE 0304-21))	130 °C
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R26	HL 1 - HL 3
Calorimetric heat release NFPA 130 (ASTM E 1354)	28 MJ/kg
Surface flammability NFPA 130 (ASTM E 162)	passed
Specific optical density of smoke NFPA 130 (ASTM E 662)	passed
Smoke gas toxicity NFPA 130 (SMP 800C)	passed

Dimensions

Width	2.2 mm
Height	29.1 mm

D-DT 2,5-QUATTRO-MT - End cover



3054419

<https://www.phoenixcontact.com/us/products/3054419>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com