

AI SORTI BOX ANT - Assortment box



3202973

<https://www.phoenixcontact.com/us/products/3202973>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assortment box, supplied with ferrules in accordance with DIN 46228-4, 50 pcs. AI 4-10 GY, 20 pcs. each AI 6-12 YE, AI 10-12 RD, 10 pcs. AI 16-12 BU

Your advantages

- Color coding and the transparent cover facilitate fast access to the required ferrules
- The practical assortment boxes are designed to keep your workshop tidy
- Using the integrated euro-clip, they can be hung up on perforated board walls, for example, to save space

Commercial data

Item number	3202973
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH34
Product key	BH3416
GTIN	4017918947118
Weight per piece (including packing)	114 g
Weight per piece (excluding packing)	103 g
Customs tariff number	85369010
Country of origin	DE

AI SORTI BOX ANT - Assortment box



3202973

<https://www.phoenixcontact.com/us/products/3202973>

Set consists of

AI 4 -10 GY - Ferrule

3200535

<https://www.phoenixcontact.com/us/products/3200535>



Ferrule, Length contact range: 10 mm, sleeve length: 17 mm, color: gray

AI 6 -12 YE - Ferrule

3200548

<https://www.phoenixcontact.com/us/products/3200548>



Ferrule, Length contact range: 12 mm, sleeve length: 20 mm, color: yellow

AI SORTI BOX ANT - Assortment box



3202973

<https://www.phoenixcontact.com/us/products/3202973>

AI 10 -12 RD - Ferrule

3200551

<https://www.phoenixcontact.com/us/products/3200551>



Ferrule, Length contact range: 12 mm, sleeve length: 22 mm, color: red

AI 16 -12 BU - Ferrule

3200564

<https://www.phoenixcontact.com/us/products/3200564>



Ferrule, Length contact range: 12 mm, sleeve length: 24 mm, color: blue

AI SORTI BOX ANT - Assortment box



3202973

<https://www.phoenixcontact.com/us/products/3202973>

Technical data

Product properties

Product type	Assortment box
--------------	----------------

Material specifications

Color	anthracite gray (RAL 7016)
Material	CU-DHP
Flammability rating according to UL 94	HB
Coating	galvanically tin-plated
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Permanent temperature	105 °C (-40 °C no load / 0 °C dynamic load)
Short-term temperature	120 °C

AI SORTI BOX ANT - Assortment box



3202973

<https://www.phoenixcontact.com/us/products/3202973>

Classifications

ECLASS

ECLASS-15.0	27400218
ECLASS-13.0	27400218

ETIM

ETIM 10.0	EC000524
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AI SORTI BOX ANT - Assortment box



3202973

<https://www.phoenixcontact.com/us/products/3202973>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com