

SKS 32-D - Shield connection terminal block



3062906

<https://www.phoenixcontact.com/us/products/3062906>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Shield connection terminal block, for direct shield on conductive mounting panels

Your advantages

- As components, it is not possible to certify shield connections in accordance with the requirements of the directive and standards for electrical equipment in potentially explosive areas. As such, shield connection clamps can be used in the Ex area even without an appropriate approval or marking.
- Three different mounting types supported: on NS 35 DIN rails, on busbars, or directly on conductive mounting panels

Commercial data

Item number	3062906
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE75
Product key	BE7521
GTIN	4046356562959
Weight per piece (including packing)	95.28 g
Weight per piece (excluding packing)	78.33 g
Customs tariff number	85369010
Country of origin	DE

SKS 32-D - Shield connection terminal block



3062906

<https://www.phoenixcontact.com/us/products/3062906>

Technical data

Product properties

Product type	Shield connection clamp
Pitch	32 mm
Number of connections	1
Number of rows	1

Electrical properties

Maximum power dissipation for nominal condition	0.77 W
---	--------

Connection data

Grounding foot	Yes
Connection method	Spring-cage connection
Conductor cross-section rigid	15 mm ² ... 32 mm ²
Cross section AWG	6 ... 2 (converted acc. to IEC)
Conductor cross-section flexible	15 mm ² ... 32 mm ²
Conductor cross-section, flexible [AWG]	6 ... 4 (converted acc. to IEC)

Dimensions

Width	32 mm
Height	36 mm
Depth	64 mm
Pitch	32 mm

External dimensions

Outside diameter	15 mm ... 32 mm
------------------	-----------------

Material specifications

Color	silver-colored
Material	Steel

Cable/line

External cable diameter	15 mm ... 32 mm
-------------------------	-----------------

Mechanical properties

Mechanical data

Open side panel	No
-----------------	----

Mounting

Mounting type	NS 35/7,5
	NS 35/15

SKS 32-D - Shield connection terminal block



3062906

<https://www.phoenixcontact.com/us/products/3062906>

Classifications

ECLASS

ECLASS-13.0	27250309
ECLASS-15.0	27250309

ETIM

ETIM 10.0	EC002020
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

SKS 32-D - Shield connection terminal block



3062906

<https://www.phoenixcontact.com/us/products/3062906>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	1.103 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com