

FBP-3/6 TR - Cover profile



3069929

<https://www.phoenixcontact.com/us/products/3069929>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover profile, depth: 32 mm, width: 74.1 mm, height: 81.5 mm, color: transparent



Commercial data

Item number	3069929
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BE06
Product key	BE6113
GTIN	4055626299938
Weight per piece (including packing)	56.8 g
Weight per piece (excluding packing)	56.1 g
Customs tariff number	39162000
Country of origin	PL

Technical data

Product properties

Product type	Cover profile
Product family	FAME 3

Insulation characteristics

Overvoltage category	III
----------------------	-----

Dimensions

Width	74.1 mm
Height	81.5 mm
Depth	32 mm

Material specifications

Color	transparent
Flammability rating according to UL 94	V0
Insulating material group	I
Insulating material	PVC

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

FBP-3/6 TR - Cover profile

3069929

<https://www.phoenixcontact.com/us/products/3069929>



Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

FBP-3/6 TR - Cover profile

3069929

<https://www.phoenixcontact.com/us/products/3069929>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com