

# CD WR - Universal wire retaining clip

3240284

<https://www.phoenixcontact.com/us/products/3240284>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Universal wire holding bracket, perforated, for wiring channels



## Commercial data

Item number	3240284
Packing unit	200 pc
Minimum order quantity	200 pc
Sales key	BE74
Product key	BE743Z
GTIN	4046356478472
Weight per piece (including packing)	3.79 g
Weight per piece (excluding packing)	3.2 g
Customs tariff number	39269097
Country of origin	DE

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Technical data

### Product properties

Product type	Wiring duct
--------------	-------------

### Dimensions

Width	76.5 mm
Height	20.1 mm
Depth	21.4 mm
Length	20.1 mm

### Material specifications

Color	stone gray (RAL 7030)
Material	PS-HF
Components	Lead-free

### Cable/line

Halogen-free	yes
--------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240284>



**VDE approval of drawings**

Approval ID: 40058456

**DNV**

Approval ID: TAE00004VN

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Classifications

### ECLASS

ECLASS-13.0	27400765
ECLASS-15.0	27400765

### ETIM

ETIM 10.0	EC001018
-----------	----------

### UNSPSC

UNSPSC 21.0	31163000
-------------	----------

# CD WR - Universal wire retaining clip



3240284

<https://www.phoenixcontact.com/us/products/3240284>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)