

RVT-PA 4 - Fastening clip

3240498

<https://www.phoenixcontact.com/us/products/3240498>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Plastic body-bound rivet, for hole diameter of 4 mm and a material thickness of 1.5 ... 6 mm



Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240498 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BH34 |
| Product key | BH34A2 |
| GTIN | 4046356520348 |
| Weight per piece (including packing) | 0.183 g |
| Weight per piece (excluding packing) | 0.154 g |
| Customs tariff number | 39269097 |
| Country of origin | DE |

RVT-PA 4 - Fastening clip

3240498

<https://www.phoenixcontact.com/us/products/3240498>



Technical data


Notes

| | |
|---------------------|---|
| Note on application | For mounting, use the UNIFOX-PVR P 4 rivet setting tool |
|---------------------|---|

Product properties

| | |
|--------------|-------------|
| Product type | Filler plug |
|--------------|-------------|

Dimensions

| | |
|-------------------------|--|
| Dimensional drawing |  |
| Diameter | 4 mm |
| Hole diameter | 4 mm |
| Min. material thickness | 6 mm |
| Max. material thickness | 1.5 mm |

Material specifications

| | |
|----------|------------------|
| Color | white (RAL 9010) |
| Material | Nylon |


RVT-PA 4 - Fastening clip

3240498

<https://www.phoenixcontact.com/us/products/3240498>



Drawings



RVT-PA 4 - Fastening clip

3240498

<https://www.phoenixcontact.com/us/products/3240498>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400766 |
| ECLASS-15.0 | 27400766 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002377 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31162200 |
|-------------|----------|

RVT-PA 4 - Fastening clip



3240498

<https://www.phoenixcontact.com/us/products/3240498>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.009 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com