

CD 60X80 WH - Cable duct



3240630

<https://www.phoenixcontact.com/us/products/3240630>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct for installation and mounting in control cabinets, white, comprising upper part and mounting base, width: 60 mm, height: 80 mm, length: 2000 mm

Your advantages

- Predetermined breaking point enables tool-free, burr-free removal of bars
- Thanks to its leverage and special cutting geometry, the PPS CD cable duct cutter enables easy, burr-free cutting with minimum effort
- Easy, burr-free cutting with minimum effort using the CUTFOX-CD cable duct cutter
- The wide, diagonal heads of the cable duct bars make it easy to fit the cover and hold it securely in place
- Installed conductors are securely held in place by means of wire retaining clips that can be snapped onto bars on the side
- Plastic body-bound rivets enable easy fixing of cable ducts using the rivet setting tool

Commercial data

Item number	3240630
Packing unit	18 pc
Minimum order quantity	18 pc
Sales key	BE74
Product key	BE7433
GTIN	4046356629461
Weight per piece (including packing)	1,358 g
Weight per piece (excluding packing)	1,255.9 g
Customs tariff number	39259020
Country of origin	DE

CD 60X80 WH - Cable duct

3240630

<https://www.phoenixcontact.com/us/products/3240630>



Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Dimensions

Width	60 mm
Height	80 mm
Length	2000 mm

Material specifications

Color	white (RAL 9010)
Material	PVC
Flammability rating according to UL 94	V0
Components	Lead-free

Cable/line

Halogen-free	no
--------------	----

Mechanical properties

Usage cross-section	4179 mm ² (100 %)
Number of cables at 60% filling volume	156 (2.5 mm ² Ø 3.4 mm)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 60 °C
---------------------------------	------------------

CD 60X80 WH - Cable duct

3240630

<https://www.phoenixcontact.com/us/products/3240630>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240630>



CSA

Approval ID: 80202282



VDE approval of drawings

Approval ID: 40058456



UL Recognized

Approval ID: E328576

CD 60X80 WH - Cable duct

3240630

<https://www.phoenixcontact.com/us/products/3240630>



Classifications

ECLASS

ECLASS-13.0	27400703
ECLASS-15.0	27400703

ETIM

ETIM 10.0	EC000012
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

CD 60X80 WH - Cable duct

3240630

<https://www.phoenixcontact.com/us/products/3240630>



Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.686 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com