

C-SCF 6/6,3X0,8 - Connector

3240160

<https://www.phoenixcontact.com/us/products/3240160>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Slip-on sleeve, non-insulated, 4 ... 6 mm², 6.3 x 0.8

Your advantages

- They round out the product range in terms of connectors
- The uninsulated slip-on sleeves and flat plugs are made from electrolytically tin-plated brass

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240160 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BH34 |
| Product key | BH3452 |
| GTIN | 4046356453776 |
| Weight per piece (including packing) | 0.965 g |
| Weight per piece (excluding packing) | 0.946 g |
| Customs tariff number | 85366990 |
| Country of origin | CZ |

C-SCF 6/6,3X0,8 - Connector

3240160


<https://www.phoenixcontact.com/us/products/3240160>

Technical data

Product properties

| | |
|------------------|-------------------------------------|
| Product type | Connector |
| Product property | Manufactured according to DIN 46247 |
| | Crimp area with embossing |
| | Tin-plated |

Dimensions

| | |
|--------------------------|--|
| Dimensional drawing |  |
| Width | 6.3 mm |
| Sleeve length | 19.2 mm |
| Maximum stripping length | 9 mm |
| Min. material thickness | 0.4 mm |

Material specifications

| | |
|---------------------|------------------|
| Color | silver-colored |
| Material | Brass |
| Coating | tin-plated |
| Insulating material | nicht zutreffend |
| Components | halogen-free |

Mechanical properties

Technical data

| | |
|---------------|---------|
| Sleeve length | 19.2 mm |
|---------------|---------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|--------|
| Ambient temperature (operation) | 110 °C |
|---------------------------------|--------|

C-SCF 6/6,3X0,8 - Connector

3240160

<https://www.phoenixcontact.com/us/products/3240160>



Drawings

Dimensional drawing



C-SCF 6/6,3X0,8 - Connector



3240160

<https://www.phoenixcontact.com/us/products/3240160>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27400212 |
| ECLASS-15.0 | 27400212 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC001059 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 27121700 |
|-------------|----------|

C-SCF 6/6,3X0,8 - Connector



3240160

<https://www.phoenixcontact.com/us/products/3240160>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.021 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com