

WT-BASE P HF 9,5 BK - Cable binder base

3240710

<https://www.phoenixcontact.com/us/products/3240710>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binder base, for cable binders of up to 9.5 mm, with fins, 8 mm drilling diameter, can be knocked in

Commercial data

Item number	3240710
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE07
Product key	BE713Z
GTIN	4046356704274
Weight per piece (including packing)	2.199 g
Weight per piece (excluding packing)	2.01 g
Customs tariff number	39269097
Country of origin	IT

WT-BASE P HF 9,5 BK - Cable binder base



3240710

<https://www.phoenixcontact.com/us/products/3240710>

Technical data

Product properties

Product type	Cable tie
--------------	-----------

Dimensions

Width	13 mm
Height	43 mm
Length	20 mm
Hole diameter	8 mm
Diameter mounting hole	8 mm

Internal dimensions

Width_inside	9.5 mm
--------------	--------

Material specifications

Color	black (RAL 9005)
Material	PA 6
Flammability rating according to UL 94	HB
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-10 °C ... 65 °C
Ambient temperature (assembly)	-5 °C ... 65 °C

Mounting

Mounting type	Drive in
---------------	----------

WT-BASE P HF 9,5 BK - Cable binder base



3240710

<https://www.phoenixcontact.com/us/products/3240710>

Classifications

ECLASS

ECLASS-13.0	23159090
ECLASS-15.0	23159090

ETIM

ETIM 10.0	EC011571
-----------	----------

UNSPSC

UNSPSC 21.0	39121700
-------------	----------

WT-BASE P HF 9,5 BK - Cable binder base



3240710

<https://www.phoenixcontact.com/us/products/3240710>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com