

WT-BASE P HF 9,5 BK - Cable binder base

3240710

<https://www.phoenixcontact.com/us/products/3240710>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binder base, for cable binders of up to 9.5 mm, with fins, 8 mm drilling diameter, can be knocked in

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240710 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE713Z |
| GTIN | 4046356704274 |
| Weight per piece (including packing) | 2.199 g |
| Weight per piece (excluding packing) | 2.01 g |
| Customs tariff number | 39269097 |
| Country of origin | IT |

WT-BASE P HF 9,5 BK - Cable binder base



3240710

<https://www.phoenixcontact.com/us/products/3240710>

Technical data

Product properties

| | |
|--------------|-----------|
| Product type | Cable tie |
|--------------|-----------|

Dimensions

| | |
|------------------------|-------|
| Width | 13 mm |
| Height | 43 mm |
| Length | 20 mm |
| Hole diameter | 8 mm |
| Diameter mounting hole | 8 mm |

Internal dimensions

| | |
|--------------|--------|
| Width_inside | 9.5 mm |
|--------------|--------|

Material specifications

| | |
|--|--------------------------------|
| Color | black (RAL 9005) |
| Material | PA 6 |
| Flammability rating according to UL 94 | HB |
| Components | free from silicone and halogen |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -10 °C ... 65 °C |
| Ambient temperature (assembly) | -5 °C ... 65 °C |

Mounting

| | |
|---------------|----------|
| Mounting type | Drive in |
|---------------|----------|

WT-BASE P HF 9,5 BK - Cable binder base



3240710

<https://www.phoenixcontact.com/us/products/3240710>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 23159090 |
| ECLASS-15.0 | 23159090 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC011571 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

WT-BASE P HF 9,5 BK - Cable binder base



3240710

<https://www.phoenixcontact.com/us/products/3240710>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com