

WP-BASE C PA HF 15,8 BK - Hose holder with cover



3240960

<https://www.phoenixcontact.com/us/products/3240960>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Hose holder with cover, material: PA, color: black, flammability rating in acc. with UL 94: V2



Commercial data

Item number	3240960
Packing unit	50 pc
Minimum order quantity	50 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356710671
Weight per piece (including packing)	4.378 g
Weight per piece (excluding packing)	4.3 g
Customs tariff number	39174000
Country of origin	DE

WP-BASE C PA HF 15,8 BK - Hose holder with cover



3240960

<https://www.phoenixcontact.com/us/products/3240960>

Technical data

Product properties

Product type	Mounting material
--------------	-------------------

Dimensions

Diameter	15.8 mm
Hole diameter	5.5 mm

Material specifications

Material	PA
Flammability rating according to UL 94	V2
Components	halogen-free

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
---------------------------------	-------------------

Mounting

Mounting type	Screw mounting
---------------	----------------

WP-BASE C PA HF 15,8 BK - Hose holder with cover



3240960

<https://www.phoenixcontact.com/us/products/3240960>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240960>



UL Recognized
Approval ID: E86359

WP-BASE C PA HF 15,8 BK - Hose holder with cover



3240960

<https://www.phoenixcontact.com/us/products/3240960>

Classifications

ECLASS

ECLASS-13.0	27430315
ECLASS-15.0	27430315

UNSPSC

UNSPSC 21.0	31162900
-------------	----------

WP-BASE C PA HF 15,8 BK - Hose holder with cover



3240960

<https://www.phoenixcontact.com/us/products/3240960>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	0.369 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com