

CD-HF 30X60 BU - Cable duct

3240587

<https://www.phoenixcontact.com/us/products/3240587>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct, blue, halogen-free, comprising upper part and mounting base, width: 30 mm, height: 60 mm, length: 2000 mm

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3240587 |
| Packing unit | 24 pc |
| Minimum order quantity | 24 pc |
| Sales key | BE74 |
| Product key | BE7442 |
| GTIN | 4046356630054 |
| Weight per piece (including packing) | 572 g |
| Weight per piece (excluding packing) | 572 g |
| Customs tariff number | 39259020 |
| Country of origin | DE |

CD-HF 30X60 BU - Cable duct



3240587

<https://www.phoenixcontact.com/us/products/3240587>

Technical data

Product properties

| | |
|--------------|-------------|
| Product type | Wiring duct |
|--------------|-------------|

Connection data

| | |
|-----------------------|----------------------|
| Nominal cross section | 1060 mm ² |
|-----------------------|----------------------|

Dimensions

| | |
|--------|---------|
| Width | 30 mm |
| Height | 2000 mm |
| Depth | 60 mm |
| Length | 2000 mm |

Material specifications

| | |
|--|------------------|
| Color | blue (RAL 5015) |
| Material | PC/ABS |
| Flammability rating according to UL 94 | V0 |
| Fire protection for rail vehicles (DIN EN 45545-2) R22 | HL 1, HL 2, HL 3 |
| Fire protection for rail vehicles (DIN EN 45545-2) R23 | HL 1, HL 2, HL 3 |
| Components | halogen-free |

Cable/line

| | |
|--------------|-----|
| Halogen-free | yes |
|--------------|-----|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|------------------|
| Ambient temperature (operation) | -25 °C ... 90 °C |
|---------------------------------|------------------|

CD-HF 30X60 BU - Cable duct



3240587

<https://www.phoenixcontact.com/us/products/3240587>

Classifications

ECLASS

ECLASS-13.0

27400703

ETIM

ETIM 9.0

EC000012

UNSPSC

UNSPSC 21.0

39131700

CD-HF 30X60 BU - Cable duct



3240587

<https://www.phoenixcontact.com/us/products/3240587>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com