

CD-HF 120X60 BU - Cable duct



3240607

<https://www.phoenixcontact.com/us/products/3240607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable duct, blue, halogen-free, comprising upper part and mounting base, width: 120 mm, height: 60 mm, length: 2000 mm

Commercial data

Item number	3240607
Packing unit	6 pc
Minimum order quantity	6 pc
Sales key	BE74
Product key	BE7442
GTIN	4046356630238
Weight per piece (including packing)	1,506 g
Weight per piece (excluding packing)	1,506 g
Customs tariff number	39259020
Country of origin	DE

CD-HF 120X60 BU - Cable duct



3240607

<https://www.phoenixcontact.com/us/products/3240607>

Technical data

Product properties

Product type	Wiring duct
--------------	-------------

Connection data

Nominal cross section	4519 mm ²
-----------------------	----------------------

Dimensions

Width	120 mm
Height	2000 mm
Depth	60 mm
Length	2000 mm

Material specifications

Color	blue (RAL 5015)
Material	PC/ABS
Flammability rating according to UL 94	V0
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1, HL 2, HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1, HL 2, HL 3
Components	halogen-free

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 90 °C
---------------------------------	------------------

CD-HF 120X60 BU - Cable duct



3240607

<https://www.phoenixcontact.com/us/products/3240607>

Classifications

ECLASS

ECLASS-13.0

27400703

ETIM

ETIM 9.0

EC000012

UNSPSC

UNSPSC 21.0

39131700

CD-HF 120X60 BU - Cable duct



3240607

<https://www.phoenixcontact.com/us/products/3240607>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com