

WP-CN BRASS M25 - Counter nut

3241149

<https://www.phoenixcontact.com/us/products/3241149>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Counter nut, for threads M25, color: silver-colored



Your advantages

- The brass counter nuts are used to lock protective hose screw connections in the case of bore holes without a thread.
- Metric thread in accordance with EN 50262

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 3241149 |
| Packing unit | 100 pc |
| Minimum order quantity | 100 pc |
| Sales key | BF68 |
| Product key | AF7DSA |
| GTIN | 4046356785556 |
| Weight per piece (including packing) | 8.6 g |
| Weight per piece (excluding packing) | 8.6 g |
| Customs tariff number | 74153300 |
| Country of origin | DE |

WP-CN BRASS M25 - Counter nut



3241149

<https://www.phoenixcontact.com/us/products/3241149>

Technical data

Product properties

| | |
|--------------|----------|
| Product type | Flat nut |
| Thread type | M25 |

Dimensions

| | |
|-----------------------------|--------|
| Height | 3.5 mm |
| Thread type connection side | M25 |

Material specifications

| | |
|----------|----------------------|
| Material | Brass, nickel-plated |
|----------|----------------------|

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|-------------------|
| Ambient temperature (operation) | -40 °C ... 200 °C |
|---------------------------------|-------------------|

WP-CN BRASS M25 - Counter nut



3241149

<https://www.phoenixcontact.com/us/products/3241149>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27140807 |
| ECLASS-15.0 | 27140807 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC003608 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 31161700 |
|-------------|----------|

WP-CN BRASS M25 - Counter nut



3241149

<https://www.phoenixcontact.com/us/products/3241149>

Environmental product compliance

EU RoHS

| | |
|---|------|
| Fulfills EU RoHS substance requirements | Yes |
| Exemption | 6(c) |

China RoHS

| | |
|--|---|
| Environment friendly use period (EFUP) | EFUP-50 |
| | An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required. |

EU REACH SVHC

| | |
|-------------------------------------|--------------------------------------|
| REACH candidate substance (CAS No.) | Lead(CAS: 7439-92-1) |
| SCIP | b8c5b402-e7e3-4f59-9014-62a4ab1db909 |

EF3.1 Climate Change

| | |
|---------|---------------|
| CO2e kg | 0.262 kg CO2e |
|---------|---------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com