

# WP-EC TPE HF 28,5 BK - Transition sleeve from hose to cable



3240978

<https://www.phoenixcontact.com/us/products/3240978>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Transition sleeve from hose to cable, material: TPE, color: black, flammability rating in acc. with UL 94: HB

## Commercial data

Item number	3240978
Packing unit	25 pc
Minimum order quantity	25 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356710961
Weight per piece (including packing)	7.004 g
Weight per piece (excluding packing)	6.976 g
Customs tariff number	39174000
Country of origin	DE

# WP-EC TPE HF 28,5 BK - Transition sleeve from hose to cable



3240978

<https://www.phoenixcontact.com/us/products/3240978>

## Technical data

### Product properties

Product type	Protective cap
--------------	----------------

### Dimensions

Length	40.2 mm
Diameter	28.5 mm

### Material specifications

Material	TPE
Flammability rating according to UL 94	HB
Components	halogen-free

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 120 °C
Short-term temperature	150 °C

# WP-EC TPE HF 28,5 BK - Transition sleeve from hose to cable



3240978

<https://www.phoenixcontact.com/us/products/3240978>

## Classifications

### ECLASS

ECLASS-15.0	27430316
ECLASS-13.0	27430316

### ETIM

ETIM 10.0	EC000519
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# WP-EC TPE HF 28,5 BK - Transition sleeve from hose to cable



3240978

<https://www.phoenixcontact.com/us/products/3240978>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)