

WP-GR HF CTA M32 BK - Protective hose screw connection

3241222

<https://www.phoenixcontact.com/us/products/3241222>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Corrugated pipe adapter, with internal thread, for connecting corrugated pipes to HEAVYCON EVO M32 plastic cable glands or ADVANCE M32 plastic housings, straight, black, IP66.

Commercial data

Item number	3241222
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BF68
Product key	AF7DSA
GTIN	4046356860840
Weight per piece (including packing)	30.39 g
Weight per piece (excluding packing)	30.39 g
Customs tariff number	39269097
Country of origin	DE

WP-GR HF CTA M32 BK - Protective hose screw connection



3241222

<https://www.phoenixcontact.com/us/products/3241222>

Technical data

Product properties

Product type	Protective hose screw connection
Application	Cable gland
Thread type	metric

Material specifications

Material	PA
Flammability rating according to UL 94	V2
Material for screw connection	PA
Components	free from silicone, halogen, and cadmium

Cable/line

Halogen-free	yes
--------------	-----

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP66
Ambient temperature (operation)	-40 °C ... 115 °C

Mounting

Assembly note	The corrugated pipe adapter is used in the screw connection instead of the union nut. Thanks to the adapter, corrugated pipes can be used.
---------------	--

WP-GR HF CTA M32 BK - Protective hose screw connection



3241222

<https://www.phoenixcontact.com/us/products/3241222>

Classifications

ECLASS

ECLASS-13.0	27430311
ECLASS-15.0	27430311

ETIM

ETIM 10.0	EC001178
-----------	----------

UNSPSC

UNSPSC 21.0	39121300
-------------	----------

WP-GR HF CTA M32 BK - Protective hose screw connection



3241222

<https://www.phoenixcontact.com/us/products/3241222>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

EF3.1 Climate Change

CO2e kg	2.396 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com