

WG-S HF 80 BK - Spiral tube



3241120

<https://www.phoenixcontact.com/us/products/3241120>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Spiral hose, for easy bundling and guiding of cables and conductors, offers protection against slight mechanical strain

Commercial data

Item number	3241120
Packing unit	20 m
Minimum order quantity	20 m
Sales key	BE74
Product key	BE7451
GTIN	4046356717496
Weight per piece (including packing)	33.4 g
Weight per piece (excluding packing)	30.8 g
Customs tariff number	39269097
Country of origin	PL

WG-S HF 80 BK - Spiral tube



3241120

<https://www.phoenixcontact.com/us/products/3241120>

Technical data

Product properties

Product type	Cable tie
--------------	-----------

Dimensions

Width	80 mm
Length	20 m

Internal dimensions

Internal diameter	12 mm
-------------------	-------

Material specifications

Color	black (RAL 9005)
Material	PE
Flammability rating according to UL 94	HB
Components	free from silicone and halogen

Cable/line

External cable diameter	15 mm ... 80 mm
-------------------------	-----------------

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-50 °C ... 85 °C
Ambient temperature (assembly)	-20 °C ... 60 °C

Mounting

Mounting type	Twist
---------------	-------

WG-S HF 80 BK - Spiral tube



3241120

<https://www.phoenixcontact.com/us/products/3241120>

Classifications

ECLASS

ECLASS-13.0	27430302
ECLASS-15.0	27430302

ETIM

ETIM 10.0	EC002604
-----------	----------

UNSPSC

UNSPSC 21.0	39131700
-------------	----------

WG-S HF 80 BK - Spiral tube



3241120

<https://www.phoenixcontact.com/us/products/3241120>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com