

# D-BT 1,25 GY - End cover

3281129

<https://www.phoenixcontact.com/us/products/3281129>



Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

End cover, width: 3.5 mm, height: 26 mm, color: gray



The figure shows a similar product in black

## Commercial data

Item number	3281129
Packing unit	50 pc
Minimum order quantity	50 pc
Product key	BE55ZX
GTIN	4055626340463
Weight per piece (including packing)	2.095 g
Weight per piece (excluding packing)	2.095 g
Country of origin	IN

# D-BT 1,25 GY - End cover

3281129

<https://www.phoenixcontact.com/us/products/3281129>



## Technical data

### Product properties

Product type	End cover
--------------	-----------

### Insulation characteristics

Overvoltage category	III
----------------------	-----

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 85 °C
Ambient temperature (storage/transport)	-25 °C ... 55 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

### Material specifications

Color	gray
Material	PC
Flammability rating according to UL 94	V0
Insulating material group	IIIa

### Dimensions

Width	3.5 mm
End cover width	3.5 mm
Height	26 mm

# D-BT 1,25 GY - End cover

3281129

<https://www.phoenixcontact.com/us/products/3281129>



## Classifications

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# D-BT 1,25 GY - End cover



3281129

<https://www.phoenixcontact.com/us/products/3281129>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)