

AP-BTO 5,5/14 - Cover profile

3281151

<https://www.phoenixcontact.com/us/products/3281151>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Cover profile, material: PC, color: transparent



Commercial data

Item number	3281151
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BE55
Product key	BE55ZX
GTIN	4055626406886
Weight per piece (including packing)	9.99 g
Weight per piece (excluding packing)	9.99 g
Customs tariff number	85389099
Country of origin	DE

AP-BTO 5,5/14 - Cover profile



3281151

<https://www.phoenixcontact.com/us/products/3281151>

Technical data

Product properties

Product type	Cover profile
--------------	---------------

Dimensions

Width	54.5 mm
Height	1000 mm
Depth	10.5 mm
Length	1000 mm

Material specifications

Color	transparent
Material	PC
Flammability rating according to UL 94	V0

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C (max. short-term operating temperature RTI Elec.)
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

AP-BTO 5,5/14 - Cover profile



3281151

<https://www.phoenixcontact.com/us/products/3281151>

Classifications

ECLASS

ECLASS-13.0	27141190
ECLASS-15.0	27141190

ETIM

ETIM 10.0	EC002848
-----------	----------

UNSPSC

UNSPSC 21.0	39121400
-------------	----------

AP-BTO 5,5/14 - Cover profile



3281151

<https://www.phoenixcontact.com/us/products/3281151>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
-----------------------------------------	--------------------

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com