

# C-PCEI 1,5/2 - Cable lug

3241215

<https://www.phoenixcontact.com/us/products/3241215>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Pin cable lug, red, 0.5 - 1.5 mm<sup>2</sup>, L1 = 12 mm, with copper sleeve incorporated, for insulation crimp

## Your advantages

- "Easy Entry" for easy and reliable conductor entry
- Halogen-free
- Electrogalvanized
- The mechanical load capacity of the connection is significantly increased by the additionally applied copper sleeve (insulation crimp)

## Commercial data

Item number	3241215
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BH34
Product key	BH3461
GTIN	4046356826204
Weight per piece (including packing)	0.938 g
Weight per piece (excluding packing)	0.938 g
Customs tariff number	85369010
Country of origin	TW

# C-PCEI 1,5/2 - Cable lug

3241215


<https://www.phoenixcontact.com/us/products/3241215>

## Technical data

### Product properties

Product type	Connector
Product property	Halogen-free
	With "Easy Entry" (conical insertion area)
	Brazed
	PA-insulated
	With copper sleeve incorporated, for insulation crimp
	Tin-plated
	Temperature range: -20°C ... +105°C

### Dimensions

Dimensional drawing	
Sleeve length	21.5 mm
Length of the insulating material sleeve	11 mm
Length contact range	10.5 mm
Min. material thickness	0.75 mm
Inner dimensions of the insulating collar	4.1 mm

### Internal dimensions

Internal diameter	1.9 mm
-------------------	--------

### Material specifications

Color	red (RAL 3001)
Material	Copper
Flammability rating according to UL 94	V2
Coating	tin-plated
Insulating material	PA
Components	halogen-free

### Mechanical properties

#### Technical data

Sleeve length	21.5 mm
---------------	---------

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-20 °C ... 105 °C
---------------------------------	-------------------

# C-PCEI 1,5/2 - Cable lug

3241215

<https://www.phoenixcontact.com/us/products/3241215>



## Drawings

Dimensional drawing



# C-PCEI 1,5/2 - Cable lug

3241215

<https://www.phoenixcontact.com/us/products/3241215>



## Classifications

### ECLASS

ECLASS-13.0	27400204
ECLASS-15.0	27400204

### ETIM

ETIM 10.0	EC001052
-----------	----------

### UNSPSC

UNSPSC 21.0	27121700
-------------	----------

# C-PCEI 1,5/2 - Cable lug

3241215

<https://www.phoenixcontact.com/us/products/3241215>



## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.025 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)