

SCM6-50 FE 10 / 18 IH5 - Screw

5026740

<https://www.phoenixcontact.com/us/products/5026740>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Screw, with metric thread



Similar figure

Your advantages

- Low temperature rise, thanks to maximum contact force
- Well-known connection principle allows worldwide use

Commercial data

| | |
|--------------------------------------|---------------|
| Item number | 5026740 |
| Packing unit | 500 pc |
| Minimum order quantity | 1,000 pc |
| Product key | ACEPBC |
| GTIN | 4046356290791 |
| Weight per piece (including packing) | 5.89 g |
| Weight per piece (excluding packing) | 5.3 g |
| Country of origin | IN |

SCM6-50 FE 10 / 18 IH5 - Screw



5026740

<https://www.phoenixcontact.com/us/products/5026740>

Technical data

Notes

| | |
|---------|---|
| General | Further information and detailed dimensions are available in the download area. |
|---------|---|

Product properties

| | |
|--------------|-------------------|
| Product type | Mounting material |
| Thread type | M6 |

Connection data

| | |
|-----------------------|--------------------|
| Nominal cross section | 35 mm ² |
|-----------------------|--------------------|

Material specifications

| | |
|----------|-------|
| Material | Steel |
|----------|-------|

Mounting

| | |
|-----------------------|-----------------|
| Drive form screw head | Allen key (IH5) |
|-----------------------|-----------------|

SCM6-50 FE 10 / 18 IH5 - Screw



5026740

<https://www.phoenixcontact.com/us/products/5026740>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-13.0 | 27141190 |
| ECLASS-15.0 | 27141190 |

ETIM

| | |
|-----------|----------|
| ETIM 10.0 | EC002848 |
|-----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121400 |
|-------------|----------|

SCM6-50 FE 10 / 18 IH5 - Screw



5026740

<https://www.phoenixcontact.com/us/products/5026740>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com