

# LB SCHRAUBE MIT ISOL. GY - Bridge screw



5029112

<https://www.phoenixcontact.com/us/products/5029112>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Bridge screw, M3, length: 30 mm, color: gray



## Commercial data

Item number	5029112
Packing unit	100 pc
Minimum order quantity	100 pc
Sales key	BE19
Product key	BE1Z2X
GTIN	4017918287122
Weight per piece (including packing)	1.399 g
Weight per piece (excluding packing)	1.366 g
Customs tariff number	74153300
Country of origin	PL

# LB SCHRAUBE MIT ISOL. GY - Bridge screw



5029112

<https://www.phoenixcontact.com/us/products/5029112>

## Technical data

### Product properties

Product type	Mounting material
--------------	-------------------

### Dimensions

Width	4.75 mm
Height	30.3 mm
Length	30.3 mm

### Material specifications

Color	gray (RAL 7042)
Material	Brass, nickel-plated
Insulating material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-60 °C ... 105 °C
Ambient temperature (storage/transport)	-25 °C ... 60 °C (for a short time, not exceeding 24 h, -60 °C to +70 °C)
Ambient temperature (assembly)	-5 °C ... 70 °C
Ambient temperature (actuation)	-5 °C ... 70 °C
Permissible humidity (storage/transport)	30 % ... 70 %

# LB SCHRAUBE MIT ISOL. GY - Bridge screw



5029112

<https://www.phoenixcontact.com/us/products/5029112>

## Classifications

### ECLASS

ECLASS-13.0	27250303
ECLASS-15.0	27250303

### ETIM

ETIM 10.0	EC000489
-----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# LB SCHRAUBE MIT ISOL. GY - Bridge screw



5029112

<https://www.phoenixcontact.com/us/products/5029112>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

### EF3.1 Climate Change

CO2e kg	0.035 kg CO2e
---------	---------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)