

# UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Side element, 11.25 mm wide, without marker groove

## Commercial data

Item number	5030266
Packing unit	50 pc
Minimum order quantity	50 pc
Note	Made to order (non-returnable)
Sales key	AC13
Product key	ACHDCA
GTIN	4017918287238
Weight per piece (including packing)	5.38 g
Weight per piece (excluding packing)	5.38 g
Customs tariff number	85389099
Country of origin	PL

# UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

## Technical data

### Product properties

Product type	Panel mounting base side part
Housing type	Press-drawn section housings
Housing series	UMK
Product family	UMK SE
Ventilation openings present	no

### Dimensions

Length	11.25 mm
--------	----------

#### External dimensions

Profile width (external)	77 mm
--------------------------	-------

#### Internal dimensions

Profile width (internal)	72.2 mm
--------------------------	---------

### Material specifications

Color (Side element)	green (RAL 6021)
Material Lateral element	PA
Flammability rating according to UL 94	V2

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C (depending on power dissipation)
---------------------------------	--

# UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/5030266>



**UL Recognized**

Approval ID: E240868

# UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

## Classifications

### ECLASS

ECLASS-13.0	27190602
ECLASS-15.0	27190602

### ETIM

ETIM 10.0	EC002779
-----------	----------

### UNSPSC

UNSPSC 21.0	31261500
-------------	----------

# UMK-SE 11,25-3 - Lateral element



5030266

<https://www.phoenixcontact.com/us/products/5030266>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)