

PSI-MODEM-SMS-REL/DC-TESTSET - Starter kit



5055908

<https://www.phoenixcontact.com/us/products/5055908>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



The figure shows a version of the article

Commercial data

Item number	5055908
Packing unit	1 pc
Minimum order quantity	1 pc
Product key	DNC4Z2
GTIN	4046356536783
Weight per piece (including packing)	3 kg
Weight per piece (excluding packing)	3 kg
Country of origin	DE

PSI-MODEM-SMS-REL/DC-TESTSET - Starter kit



5055908

<https://www.phoenixcontact.com/us/products/5055908>

Set consists of

PSI-MODEM-SMS-REL/6ADI/4DO/DC - Signaling system

2313520

<https://www.phoenixcontact.com/us/products/2313520>



SMS remote control and signaling system for mounting on EN DIN rail. Installation built-in device as per DIN 43880. 6 analog or digital configurable inputs and 4 relay outputs. Supply voltage 24 V DC. Scope of supply: SMS relay, antenna, software, RS-232 cable.

CM-KBL-RS232/USB - Cable

2881078

<https://www.phoenixcontact.com/us/products/2881078>

Connecting cable D-9-SUB to USB, with adapter D-9-SUB to D-25-SUB.



PSI-MODEM-SMS-REL/DC-TESTSET - Starter kit

5055908

<https://www.phoenixcontact.com/us/products/5055908>



PSI-GSM/UMTS-QB-ANT - Antenna

2313371

<https://www.phoenixcontact.com/us/products/2313371>

GSM UMTS antenna, with omnidirectional characteristic, 2 m antenna cable with SMA round connector



PSI-MODEM-SMS-REL/DC-TESTSET - Starter kit



5055908

<https://www.phoenixcontact.com/us/products/5055908>

Technical data

Product properties

Product type	Starter kit
--------------	-------------

PSI-MODEM-SMS-REL/DC-TESTSET - Starter kit



5055908

<https://www.phoenixcontact.com/us/products/5055908>

Environmental product compliance

China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com