

FLKM HDSUB-26/F - Termination board



5528341

<https://www.phoenixcontact.com/us/products/5528341>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



VARIOFACE module, with screw connection and High Density D-Subminiature female connector, for mounting on NS 32 or NS 35/7.5, no. of pos.: 26, width: 79 mm

Commercial data

Item number	5528341
Packing unit	1 pc
Note	Made to order (non-returnable)
Sales key	NULL
Product key	DK2182
GTIN	4017918900816
Weight per piece (including packing)	193.3 g
Weight per piece (excluding packing)	193.3 g
Customs tariff number	85369010
Country of origin	US

FLKM HDSUB-26/F - Termination board



5528341

<https://www.phoenixcontact.com/us/products/5528341>

Technical data

Product properties

Product type	Interface module
Number of positions	26

Electrical properties

Nominal voltage U_N	125 V
Max. current carrying capacity per branch	1 A

Connection data

Field level

Connection in acc. with standard	IEC / EN
Connection method	Screw connection
Stripping length	8 mm
Screw thread	M3
Number of positions	26
Conductor cross-section rigid	0.2 mm ² ... 4 mm ²
Conductor cross-section flexible	0.2 mm ² ... 2.5 mm ²
Conductor cross-section AWG	24 ... 12

Controller level

Connection method	D-SUB socket strip
Number of positions	26

Signaling

Status display present	no
------------------------	----

Dimensions

Item dimensions

Width	79 mm
Height	77 mm
Depth	58 mm

Material specifications

Color	green (RAL 6021)
Housing insulation material	Polyamide PA non-reinforced

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C

FLKM HDSUB-26/F - Termination board



5528341

<https://www.phoenixcontact.com/us/products/5528341>

Mounting

Mounting position	any
-------------------	-----

Notes

Notes on operation	For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met.
--------------------	--

FLKM HDSUB-26/F - Termination board




5528341


<https://www.phoenixcontact.com/us/products/5528341>

Drawings

Schematic diagram



Circuit diagram



Universal circuit diagram

FLKM HDSUB-26/F - Termination board



5528341

<https://www.phoenixcontact.com/us/products/5528341>

Environmental product compliance

EU REACH SVHC

REACH candidate substance (CAS No.)	
-------------------------------------	--

	No substance above 0.1 wt%
--	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com