

UCT-PMP (90X38) VT CUS - Insert label



8190707

<https://www.phoenixcontact.com/us/products/8190707>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Insert label, Sheet, violet (RAL 4005), labeled according to customer specifications, mounting type: snapped into marker carrier, Number of individual labels: 1



Your advantages

- The UCT-PMP (90x38) system marking label is easy to mount and, if necessary, remove
- The wide temperature range means that the labels can be used in control cabinets as well as the field
- The sheets provide space for including function texts
- Marking service: Phoenix Contact can custom-mark all labels according to your requirements

Commercial data

Item number	8190707
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Product key	BG8148
GTIN	4046356965699
Weight per piece (including packing)	99.99 g
Weight per piece (excluding packing)	99.99 g
Country of origin	PL

UCT-PMP (90X38) VT CUS - Insert label



8190707

<https://www.phoenixcontact.com/us/products/8190707>

Technical data

Product properties

Product type	Plant marker
--------------	--------------

Marking

Number of individual labels	1
Number of individual labels per row	1
Identification technology	UV LED technology, direct laser marking

Dimensions

Width	90.00 mm
Height	38.00 mm
Depth	1.15 mm

Material specifications

RoHS compliant	yes
Color	violet (RAL 4005)
Flammability rating according to UL 94	V0
Base element material	PC
Relative insulation material temperature index (Elec., UL 746 B)	130 °C
Fire protection for rail vehicles (DIN EN 45545-2) R22	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R23	HL 1 - HL 3
Fire protection for rail vehicles (DIN EN 45545-2) R24	HL 1 - HL 3
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C
---------------------------------	------------------

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Mounting

Mounting type	snapped into marker carrier
---------------	-----------------------------

UCT-PMP (90X38) VT CUS - Insert label



8190707

<https://www.phoenixcontact.com/us/products/8190707>

Classifications

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

UCT-PMP (90X38) VT CUS - Insert label



8190707

<https://www.phoenixcontact.com/us/products/8190707>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com