

VIP-CAB-FLK20/FS/FS/HF/ 3,0M - Cable



2908607

<https://www.phoenixcontact.com/us/products/2908607>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled, halogen-free round cable; connection 1: IDC/FLK socket strip (1x 20-position, 180 °-out put); connection 2: IDC/FLK socket strip (1x 20-position, 180 °-out put); cable length: 3 m

Commercial data

| | |
|--------------------------------------|--------------------------------|
| Item number | 2908607 |
| Packing unit | 1 pc |
| Note | Made to order (non-returnable) |
| Sales key | C423 |
| Product key | DK2227 |
| GTIN | 4055626312767 |
| Weight per piece (including packing) | 240 g |
| Customs tariff number | 85444290 |
| Country of origin | DE |

Technical data

Product properties

| | |
|--------------|--------------|
| Product type | System cable |
|--------------|--------------|

Insulation characteristics: Air clearances and creepage distances

| | |
|----------------------|-----------------------|
| Insulation | Functional insulation |
| Overvoltage category | II |
| Pollution degree | 2 |

Environmental and real-life conditions

Ambient conditions

| | |
|---|--|
| Degree of protection | IP00 |
| Degree of protection (Installation location) | ≥ IP54 (Installation location) |
| Ambient temperature (operation) (fixed installation) | -40 °C ... 70 °C (fixed installation) |
| Ambient temperature (operation) (flexible installation) | -10 °C ... 70 °C (flexible installation) |
| Ambient temperature (storage/transport) | -40 °C ... 80 °C |
| Altitude | ≤ 2000 m |

Electrical properties

| | |
|--------------------------|-----------------------|
| Operating voltage (AC) | ≤ 25 V AC |
| Operating voltage (DC) | ≤ 60 V DC |
| Nominal operating mode | 100% operating factor |
| Current (Per path, 50°C) | ≤ 1 A |
| Current (Per path) | ≤ 0.6 A |

Air clearances and creepage distances

| | |
|--------------------------|--------|
| Rated insulation voltage | 63 V |
| Rated surge voltage | 0.6 kV |

Cable/line

| | |
|---------------------------------|-------------------------------------|
| Cable length | 3 m |
| UL AWM Style | 2464/1061 |
| Number of positions | 20 |
| Shielded | no |
| Conductor type | Assembled, halogen-free round cable |
| Conductor structure signal line | 7x 0.16 mm |
| AWG signal line | 26 |
| Conductor cross-section | 20x 0.14 mm ² |
| Wire diameter incl. insulation | 1 mm ±0.03 mm |
| External cable diameter | 7.10 mm ±0.4 mm |
| Outer sheath, material | FR-PE, halogen-free |
| External sheath, color | gray |
| Conductor material | Tin-plated Cu litz wires |

VIP-CAB-FLK20/FS/FS/HF/ 3,0M - Cable



2908607

<https://www.phoenixcontact.com/us/products/2908607>

| | |
|---|---|
| Cable resistance | ≤ 145 Ω/km (20 °C) |
| Insulation resistance | ≥ 20 MΩ*km (20 °C) |
| Smallest bending radius, fixed installation | 60 mm |
| Smallest bending radius, movable installation | 113 mm |
| Dynamic load capacity (bending) | Max. bending cycles: 5000 (at a radius of ≥ 15x outside diameter) |
| Halogen-free | yes |
| Flame resistance | IEC 60332-1-2 (raw cable) |
| | VDE 0842, Part 332-1-2 (raw cable) |
| | IEC 60332-3-22 (raw cable) |
| Resistance to oil | can withstand occasional splashes (raw cable) |
| Cable type | Cable for one module |

Connection data

Field level

| | |
|----------------------------------|----------------------|
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 20 |
| Exit angle | 180 ° |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Controller level

| | |
|----------------------------------|----------------------|
| Connection in acc. with standard | IEC 60603-13 |
| Connection method | IDC/FLK socket strip |
| Number of connections | 1 |
| Number of positions | 20 |
| Exit angle | 180 ° |
| Insertion/withdrawal cycles | > 50 |
| Pitch | 2.54 mm |

Standards and regulations

Air clearances and creepage distances

| | |
|-----------------------|--------------|
| Standards/regulations | DIN EN 50178 |
|-----------------------|--------------|

Notes

| | |
|--------------------|--|
| Notes on operation | For proper use, the specifications of the installation directive (see Downloads) must be observed. For applications or use with third-party products, the specifications, and the safety and warning instructions of the respective third-party manufacturer must also be met. |
|--------------------|--|

Drawings

Diagram



Maximum permissible current per path in uncoiled state

VIP-CAB-FLK20/FS/FS/HF/ 3,0M - Cable



2908607

<https://www.phoenixcontact.com/us/products/2908607>

Classifications

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121620 |
|-------------|----------|

VIP-CAB-FLK20/FS/FS/HF/ 3,0M - Cable



2908607

<https://www.phoenixcontact.com/us/products/2908607>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2026 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com