

EML-HA (60X30)R SR - Label for rough surfaces



0830617

<https://www.phoenixcontact.com/de/products/0830617>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label for rough surfaces, Roll, unmarked, can be labeled with: THERMOMARK E.300 (D)/600 (D), THERMOMARK ROLL 2.0, THERMOMARK ROLL, THERMOMARK ROLL X1, THERMOMARK ROLLMASTER 300/600, THERMOMARK X1.2, mounting type: adhesive, Number of individual labels: 1000, text field height: 30 mm, text field width: 60 mm

Your advantages

- The EML-HA ... self-adhesive device markers are suitable for identification of various types of equipment in controller, system, and control cabinet building
- The EML-HA features a special adhesive with a very high bonding strength. This means it can be stuck onto rough, textured, and low-energy surfaces
- When combined with the right ink ribbon, the marking is highly resistant to solvents and mechanical influences
- The EML-HA ... materials are UL-listed
- Marking service: Phoenix Contact can custom-mark all EML-HA ... markers according to your requirements

Commercial data

Item number	0830617
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BH
Product key	BG2411
GTIN	4046356719711
Weight per piece (including packing)	486 g
Weight per piece (excluding packing)	486 g
Customs tariff number	39269097
Country of origin	PL

EML-HA (60X30)R SR - Label for rough surfaces



0830617

<https://www.phoenixcontact.com/de/products/0830617>

Technical data

Product properties

Product type	Device marker
Product property	highly adhesive

Marking

Number of individual labels	1000
Number of individual labels per row	1
Identification technology	Thermotransfer

Dimensions

Width	60.00 mm
Height	30.00 mm
Depth	0.11 mm

Text field

Text field width	60 mm
Text field height	30 mm

Material specifications

RoHS compliant	yes
Foil strength	56 µm
Adhesive strength	65 µm
Color	silver-colored
Material	Polyester
Base element material	Polyester
Components	free from silicone and halogen

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-40 °C ... 105 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 %

Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VW PV 3.10.7:2005-02
Result	Test passed

UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

EML-HA (60X30)R SR - Label for rough surfaces



0830617

<https://www.phoenixcontact.com/de/products/0830617>

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN EN ISO 22479:2022-08
Result	Test passed
Procedure	Method B
Cycles	2

Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

Mounting

Mounting type	adhesive
---------------	----------

EML-HA (60X30)R SR - Label for rough surfaces



0830617

<https://www.phoenixcontact.com/de/products/0830617>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/de/products/0830617>



CSA

Approval ID: 70191766



cULus Recognized

Approval ID: MH48542

EML-HA (60X30)R SR - Label for rough surfaces



0830617

<https://www.phoenixcontact.com/de/products/0830617>

Classifications

ECLASS

ECLASS-13.0	27281103
ECLASS-15.0	27281103

ETIM

ETIM 10.0	EC001288
-----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

EML-HA (60X30)R SR - Label for rough surfaces



0830617

<https://www.phoenixcontact.com/de/products/0830617>

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements

Yes, No exemptions

EU REACH SVHC

REACH candidate substance (CAS No.)

No substance above 0.1 wt%

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Deutschland GmbH

Flachmarktstraße 8

D-32825 Blomberg

+49 52 35/3-1 20 00

info@phoenixcontact.de