

IB IL 24 PSDI 8-PAC - Safety module



2985688

<https://www.phoenixcontact.com/gb/products/2985688>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Safety-related digital input module, IP20 protection, for the SafetyBridge, INTERBUS-Safety, and PROFIsafe system. The module has 4 safe digital inputs for two-channel assignment or 8 safe digital inputs for single-channel assignment.

Product description

The safety module is an input module from the Inline product range designed for use at any point within a SafetyBridge, INTERBUS-Safety or PROFIsafe system. The transmission speed of the safety module can be set to 500 kBaud or 2 Mbaud using a switch. One transmission speed must be used consistently within a station. The module has four safe digital inputs for two-channel assignment or eight digital inputs for single-channel assignment.

Your advantages

- SIL 3 according to IEC/EN 61508
- SIL 3 in accordance with EN IEC 62061
- PL e in accordance with EN ISO 13849-1

Commercial data

Item number	2985688
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNA421
Product key	DNA421
Catalog page	Page 267 (C-6-2019)
GTIN	4046356131582
Weight per piece (including packing)	350.5 g
Weight per piece (excluding packing)	349.4 g
Customs tariff number	85389091
Country of origin	DE

IB IL 24 PSDI 8-PAC - Safety module




2985688

<https://www.phoenixcontact.com/gb/products/2985688>

Technical data

Dimensions

Dimensional drawing	
Width	48.8 mm
Height	119.8 mm
Depth	71.5 mm
Note on dimensions	Housing dimensions

Notes

Note on application

Note on application	Only for industrial use
---------------------	-------------------------

Interfaces

Inline local bus

No. of channels	2
Connection method	Inline data jumper
Transmission speed	500 kbps / 2 Mbps (can be switched)

System properties

Module

ID code (dec.)	163
ID code (hex)	A3
Length code (hex)	04
Length code (dec)	04
Process data channel	8 Byte
Input address area	8 Byte ((Operating mode: SafetyBridge))
Output address area	8 Byte ((Operating mode: SafetyBridge))
Register length	8 Byte
Required parameter data	1 Byte ((Operating mode: SafetyBridge))
Required configuration data	5 Byte ((Operating mode: SafetyBridge))

Input data

Digital:

Input name	Digital inputs
Description of the input	IEC 61131-2 type 3

IB IL 24 PSDI 8-PAC - Safety module



2985688

<https://www.phoenixcontact.com/gb/products/2985688>

Number of inputs	4 (for 2-channel assignment) 8 (for 1-channel assignment)
Cable length	max. 200 m (200 m from the clock output to the safe input (total based on forward and return path))
Connection method	Spring-cage connection
Connection technology	2-, 3-, 4-conductor
Input voltage	24 V DC (via clock outputs UT1 and UT2 or external supply)
Input voltage range	-3 V DC ... 30 V DC
Input voltage range "0" signal	-3 V DC ... 5 V DC
Input voltage range "1" signal	11 V DC ... 30 V DC
Typical input current per channel	4.2 mA (at 24 V)
Typical response time	See technical data

Product properties

Product type	I/O component
Product family	Inline
Application	Functional safety
Type	modular

Electrical properties

Maximum power dissipation for nominal condition	24.12 W
Transmission medium	Copper

Potentials: Communications power (U_L)

Supply voltage	7.5 V DC (see safety data)
Current draw	max. 180 mA

Potentials: Main circuit supply (U_M)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple)
Current draw	max. 825 mA (see safety data) typ. 25 mA (plus current consumption of the inputs when supplied via the clock outputs, plus current consumption of the connected initiators when via through the clock outputs)

Supply: Module electronics

Supply voltage	24 V DC (via voltage jumper)
Supply voltage range	19.2 V DC ... 30 V DC

Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply, incoming remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 5 V supply, outgoing remote bus/7.5 V supply (bus logics)	500 V AC, 50 Hz, 1 min
Test voltage: 7.5 V supply (bus logics)/24 V supply (I/O)	500 V AC, 50 Hz, 1 min
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 50 Hz, 1 min

Connection data

IB IL 24 PSDI 8-PAC - Safety module



2985688

<https://www.phoenixcontact.com/gb/products/2985688>

Connection technology

Connection name	Inline connector
pluggable	yes

Conductor connection

Connection method	Spring-cage connection
Conductor cross section rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross section flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16

Inline connector

Connection method	Spring-cage connection
Conductor cross section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 55 °C
Degree of protection	IP20
Air pressure (operation)	80 kPa ... 108 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	66 kPa ... 108 kPa (up to 3500 m above sea level)
Ambient temperature (storage/transport)	-25 °C ... 70 °C
Permissible humidity (operation)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)
Permissible humidity (storage/transport)	10 % ... 85 % (Take suitable measures against increased air humidity within the permitted temperature range.)

Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

IB IL 24 PSDI 8-PAC - Safety module




2985688

<https://www.phoenixcontact.com/gb/products/2985688>


Drawings

Dimensional drawing



Dimensions (in mm)

Connection diagram



Connection example for an emergency stop circuit

IB IL 24 PSDI 8-PAC - Safety module



2985688

<https://www.phoenixcontact.com/gb/products/2985688>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2985688>



Functional Safety

Approval ID: 968/FSP 2449.00/22



Functional Safety

Approval ID: 968/FSP 2449.00/22

PROFIsafe

Approval ID: Z20079



Functional Safety

Approval ID: 968/EZ 650.04/20



Functional Safety

Approval ID: 968/EZ 650.04/20



cULus Listed

Approval ID: E140324

IB IL 24 PSDI 8-PAC - Safety module



2985688

<https://www.phoenixcontact.com/gb/products/2985688>

Classifications

ECLASS

ECLASS-11.0	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604

ETIM

ETIM 9.0	EC001599
----------	----------

UNSPSC

UNSPSC 21.0	32151600
-------------	----------

Environmental product compliance

EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a), 7(c)-I

China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	aa3b175d-1dc9-4105-81b3-1536a8212398

EF3.0 Climate Change

CO2e kg	15.87 kg CO2e
---------	---------------