

AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



PLCnext Control for the direct control of Axioline F I/Os. With two Ethernet interfaces. Complete with connector and bus base module.

Product description

The PLCnext AXC F 2152 controller for the Axioline I/O system is fast, robust and easy to use. It has been consistently designed for maximum performance, easy handling and use in harsh industrial environments.

Your advantages

- Linux operating system
- Supports high-level languages
- Up to 63 AXIO I/O modules can be mounted side by side
- 2x Ethernet interfaces (integrated switch)
- Increased resistance to EMI
- Extended temperature range of -25 °C ... 60 °C
- PROFINET support
- Connection to PROFICLOUD
- Numerous protocols supported such as: http, https, FTP, OPC UA, SNMP, SMTP, SQL, MySQL, DCP, etc.
- Connection to the PLCnext Store

Commercial data

Item number	2404267
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR09
Product key	DRADAC
Catalog page	Page 10 (C-6-2019)
GTIN	4055626356280
Weight per piece (including packing)	278.633 g
Weight per piece (excluding packing)	223 g
Customs tariff number	85371091
Country of origin	DE

Technical data

Product properties

Type	modular
Product type	Controller
Product family	PLCnext Control

Insulation characteristics

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
Overvoltage category	II
Pollution degree	2

Display

Diagnostics display	No
---------------------	----

System properties

Processor	Arm® Cortex®-A9 2x 800 MHz
Flash memory	512 Mbyte (internal flash memory) SD card from Phoenix Contact (for external flash memory, see accessories)
Retentive data storage	48 kByte (NVRAM)
RAM	512 Mbyte DDR3 SDRAM

IoT capability: PROFICLOUD

IoT platform	PROFICLOUD
Supports cloud computing	yes

IEC 61131 runtime system

Program memory	8 Mbyte
Data storage system	12 Mbyte

Axioline

Amount of process data	max. 1482 Byte (per station (total input and output data))
	max. 1024 Byte (Axioline F local bus (input))
	max. 1024 Byte (Axioline F local bus (output))
Number of supported devices	max. 63 (per station)
Number of local bus devices that can be connected	max. 63 (observe current consumption)

PROFINET

Device function	PROFINET controller, PROFINET device
Update rate	min. 1 ms (4 devices)
	min. 16 ms (64 devices)
Conformance Class	B
Number of supported devices	max. 64 (at PROFINET controller)
Supported functions	MRP FSU PROFINET controller
	MRP PROFINET device

AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

Device ID	0142 _{hex}
Vendor ID	00B0 _{hex}

Function

Diagnostics display	No
Controller redundancy	yes
Safety function	No

Functionality

Programming languages supported	Symbolic flowchart (SFC)
	Instruction list (IL)
	Ladder diagram (LD)
	Function block diagram (FBD)
	Structured text (ST)
	C++
	C#
	Java
	Python
Simulink	

System requirements

Engineering tool	PLCnext Engineer
	Eclipse
	Visual Studio
	MATLAB® Simulink®
Application interface	OPC UA

Electrical properties

Real-time clock

Realtime clock	Yes
Description realtime clock	1.73 s/day = 20 ppm at 25 °C

Potentials: Communications power U_L feed-in (the supply of the Axioline F local bus U_{BUS} is generated from U_L)

Supply voltage	24 V DC
Supply voltage range	19.2 V DC ... 30 V DC (including all tolerances, including ripple ($\pm 5\%$))
Current draw	max. 442 mA (with 1 A at U_{BUS} for the I/Os and $U_L = 24$ V)
Power consumption	max. 10.6 W (with 1 A at U_{BUS} for the I/Os and $U_L = 24$ V)
Protective circuit	Surge protection; electronic
	Reverse polarity protection; electronic

Potentials: Axioline F local bus supply (U_{BUS})

Supply voltage	5 V DC (via bus base module)
Power supply unit	1 A

Connection data

AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

Axioline F connector

Connection method	Push-in connection
Conductor cross section, rigid	0.2 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.2 mm ² ... 1.5 mm ²
Conductor cross section AWG	24 ... 16
Stripping length	8 mm

Interfaces

Supported protocols	HTTP
	HTTPS
	PROFINET
	INTERBUS
	Modbus/TCP (via corresponding library)
	Modbus/RTU (via corresponding library)
	Ethernet/IP (Adapter)
	CANopen [®] (via corresponding library)
	DALI (via corresponding library)
	DALI2 (via corresponding app)
	HART (via corresponding app)
	IO-Link (via corresponding app)
	PROFIBUS
	MQTT (via corresponding app)
	OPC UA Server
	OPC UA Client (via corresponding app)
	DHCP (via corresponding app)
	SFTP
	SMTP (via corresponding app)
	SNTP (via corresponding app)
SNMP (via corresponding app)	
DNS (via corresponding app)	
DNP3 (via corresponding app)	
IEC 60870-5-1 (via corresponding library)	
IEC 60870-5-104 (via corresponding library)	
IPsec	
syslog	
Web server	yes

Axioline F local bus

Number of interfaces	1
Connection method	Bus base module
Transmission speed	100 Mbps

Ethernet

Bus system	RJ45
------------	------

AXC F 2152 - Controller




2404267

<https://www.phoenixcontact.com/us/products/2404267>

Number of interfaces	2 (Switched internally)
Connection method	RJ45 jack
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps (full duplex)
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	max. 100 m

Dimensions

Dimensional drawing	
Width	45 mm
Height	126.93 mm
Depth	75 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 60 °C up to 2000 m above mean sea level (observe derating) -25 °C ... 55 °C up to 3000 m above mean sea level (observe derating) 55 °C (with max. 1 A on U _{Bus}) 55 °C ... 60 °C (only in conjunction with an Axioline F power module AXL F PWR 1H (Item no. 2688297))
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (according to DIN EN 61131-2)
Permissible humidity (storage/transport)	5 % ... 95 % (according to DIN EN 61131-2)
Shock (operation)	30g (in accordance with EN 60068-2-27/IEC 60068-2-27)
Vibration (operation)	5g (in accordance with EN 60068-2-6/IEC 60068-2-6)
Air pressure (operation)	70 kPa ... 106 kPa (up to 3000 m above sea level)
Air pressure (storage/transport)	58 kPa ... 106 kPa (up to 4500 m above mean sea level)

Approvals

ATEX

Identification	Ⓔ II 3 G Ex ec IIC T4 Gc
Certificate	TÜV 19 ATEX 8356 X

IECEX

AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

Identification	Ex ec IIC T4 Gc
Certificate	IECEX TUR 19.0031X

CCC / China-Ex

Identification	Ex ec IIC T4 Gc
Certificate	CCC Ex IIC T4 Gc

UL Ex, USA / Canada

Identification	Class I, Zone 2, AEx nA IIC T4
	Class I, Div. 2, Groups A, B, C, D
	Ex nA IIC Gc T4
Certificate	E366272

UL, USA/Canada

Identification	cULus
Certificate	E238705

Corrosive gas test

Identification	ISA S71.04.2013 G3 Harsh Group A, DIN EN 60068-2-60:2016-06 Method 4
----------------	--

Industrial Cyber Security

Identification	Industrial IT Security, IACS Component
Certificate	IITS2 029429 0027
Note	Configuration: Security Profile active

EMC data

Conformance with EMC directives	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Electrostatic discharge (ESD)EN 61000-4-2/IEC 61000-4-2 Criterion B, 6 kV contact discharge, 8 kV air discharge
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Electromagnetic fieldsEN 61000-4-3/IEC 61000-4-3 Criterion A, Field intensity: 10 V/m
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Fast transients (burst)EN 61000-4-4/IEC 61000-4-4 Criterion B, 2 kV
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Transient overvoltage (surge)EN 61000-4-5/IEC 61000-4-5 Criterion B; DC supply lines: ± 0.5 kV/ ± 1.0 kV (symmetrical/asymmetrical), fieldbus cable shielding: ± 1.0 kV
	Immunity test in accordance with EN 61000-6-2/IEC 61000-6-2 Conducted interferenceEN 61000-4-6/IEC 61000-4-6 Criterion A, Test voltage 10 V
	Noise emission test in accordance with EN 61000-6-4/IEC 61000-6-4
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU

Mounting

Mounting type	DIN rail mounting
---------------	-------------------

AXC F 2152 - Controller


2404267

<https://www.phoenixcontact.com/us/products/2404267>



Drawings

Dimensional drawing



AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2404267>



DNV GL

Approval ID: TAA00000DF



LR

Approval ID: LR2001902TA-08



NK

Approval ID: 14A006



BV

Approval ID: 36433/B4 BV



PRS

Approval ID: TE/1020/880590/21

BSH

Approval ID: 840



RINA

Approval ID: ELE283021XG

ABS

Approval ID: 23-2449604-PDA

PROFINET

Approval ID: Z13493

PROFINET

Approval ID: Z13493



TÜV SÜD Type tested

Approval ID: IITS2 029429 0027

AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

PROFINET

Approval ID: Z13494

PROFINET

Approval ID: Z13494

UAE-RoHS

Approval ID: 23-02-63241

ABS

Approval ID: 23-2449604-PDA

BSH

Approval ID: 840



BV

Approval ID: 36433/B4 BV



DNV GL

Approval ID: TAA00000DF



PRS

Approval ID: TE/1020/880590/21



NK

Approval ID: 14A006



RINA

Approval ID: ELE283021XG



LR

Approval ID: LR2001902TA-08

PROFINET

Approval ID: Z13024

AXC F 2152 - Controller



2404267

<https://www.phoenixcontact.com/us/products/2404267>

PROFINET

Approval ID: Z13024

PROFINET

Approval ID: Z13146

PROFINET

Approval ID: Z13146



cULus Listed

Approval ID: E238705



cULus Listed

Approval ID: E238705



TÜV SÜD Type tested

Approval ID: IITS2 029429 0027

UAE-RoHS

Approval ID: 23-02-63241



IECEx

Approval ID: IECEx TUR 19.0031X



cULus Listed

Approval ID: FILE E 366272



ATEX

Approval ID: TÜV 19 ATEX 8356 X



CCC

Approval ID: 2021122304114448



cULus Listed

Approval ID: FILE E 366272

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



IECEx

Approval ID: IECEx TUR 19.0031X



ATEX

Approval ID: TÜV 19 ATEX 8356 X

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



Classifications

ECLASS

ECLASS-11.0	27242207
ECLASS-12.0	27242207
ECLASS-13.0	27242207

ETIM

ETIM 9.0	EC000236
----------	----------

UNSPSC

UNSPSC 21.0	32151700
-------------	----------

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 50 years
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



Accessories

PLCNEXT ENGINEER - Programming software

1046008

<https://www.phoenixcontact.com/us/products/1046008>



Engineering software platform for Phoenix Contact automation controllers. PLCnext Engineer is IEC 61131-3-compliant and is available free of charge under Downloads. Its functionality can be extended using paid add-ins. To do this, open the license configurator via the "Configure" button.

SD FLASH 8GB PLCNEXT MEMORY - Program / configuration memory

1061701

<https://www.phoenixcontact.com/us/products/1061701>



Program and configuration memory for storing the application programs and other files in the file system of the PLC, plug-in, 8 GB.

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



SD FLASH 2GB PLCNEXT MEMORY - Program / configuration memory

1043501

<https://www.phoenixcontact.com/us/products/1043501>



Program and configuration memory for storing the application programs and other files in the file system of the PLC, plug-in, 2 GB.

SD FLASH 8GB PLCNEXT MEMORY LIC - Program / configuration memory

1151112

<https://www.phoenixcontact.com/us/products/1151112>



Program and configuration memory for storing the application programs, licenses, and other files in the file system of the PLC, plug-in, 8 GB.

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



SD FLASH 32GB PLCNEXT MEMORY LIC - Program / configuration memory

1151111

<https://www.phoenixcontact.com/us/products/1151111>



Program and configuration memory for storing the application programs, licenses, and other files in the file system of the PLC, plug-in, 32 GB.

AXC BS L 2 - Bus connector

1064312

<https://www.phoenixcontact.com/us/products/1064312>



Bus base module for the left alignment of AXC F XT... type extension modules to AXC F 2152 type controllers (item no. 2404267).

AXC F 2152 - Controller

2404267


<https://www.phoenixcontact.com/us/products/2404267>



AXL F PWR 1H - Power module

2688297

<https://www.phoenixcontact.com/us/products/2688297>



Axioline F, Power module for the logic supply U_{Bus} , max. 4 A, degree of protection: IP20, including bus base module and Axioline F connector

AXC F IL ADAPT - PLC extension module

1020304

<https://www.phoenixcontact.com/us/products/1020304>



Right-alignable Inline adapter terminal (INTERBUS master) for one PLCnext Control device for setting up a PLCnext Technology Inline station

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



AXC F XT ETH 1TX - PLC extension module

2403115

<https://www.phoenixcontact.com/us/products/2403115>



Left-alignable Ethernet interface, for connection to a compatible modular controller from the PLCnext Control range.

AXC F XT IB - PLC extension module

2403018

<https://www.phoenixcontact.com/us/products/2403018>



Left-alignable INTERBUS master, for the connection of INTERBUS remote bus components to a compatible modular controller from the PLCnext Control range.

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



AXC F XT PB - PLC extension module

1091657

<https://www.phoenixcontact.com/us/products/1091657>



Left-alignable PROFIBUS master, for the connection of PROFIBUS components to a compatible modular controller from the PLCnext Control series.

AXC F XT KIT - PLC extension module

1383116

<https://www.phoenixcontact.com/us/products/1383116>



Left-alignable extension module equipped with a Mini PCIe slot for connection to a type AXC F 2152 or AXC F 3152 PLCnext controller

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



AXC F XT EXP - PLC extension module

1139999

<https://www.phoenixcontact.com/us/products/1139999>



Left-alignable PCIe extension interface, for connection to a compatible modular controller from the PLCnext Control range.

AXC F XT SPLC 1000 - PLC extension module

1159811

<https://www.phoenixcontact.com/us/products/1159811>



The AXC F XT SPLC 1000 is a left-alignable, safety-oriented controller for operating PROFIsafe devices. The SPLC 1000 is connected to the AXC F 2152 or AXC F 3152 modular controllers from the PLCnext Control series.

AXC F 2152 - Controller

2404267

<https://www.phoenixcontact.com/us/products/2404267>



AXC F XT SPLC 3000 - PLC extension module

1160157

<https://www.phoenixcontact.com/us/products/1160157>



The AXC F XT SPLC 3000 is a left-alignable, safety-oriented controller for operating PROFIsafe devices. The SPLC 3000 is connected to the AXC F 2152 or AXC F 3152 modular controllers from the PLCnext Control series.

AXL F BS BK - Bus connector

2701422

<https://www.phoenixcontact.com/us/products/2701422>



Axioline F bus base module for housing type BK

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com