

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch



2891079

<https://www.phoenixcontact.com/gb/products/2891079>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Rack-mount managed Ethernet switch meets IEC 61850-3 and IEEE 1613. Provides eight RJ45 ports at 10/100 Mbps, 16 SC-D MM fiber ports at 100 Mbps and four gigabit combo ports (10/100/1000 Mbps RJ45 connection; 1000 Mbps fiber optic connection requires 1000 Mbps SFP module).



## Product description

Developed according to IEC 61850-3 (Ambient conditions)

## Your advantages

- Network structure according to IEC 61850
- IEEE 1613

## Commercial data

Item number	2891079
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DNN125
Product key	DNN125
Catalog page	Page 321 (C-6-2019)
GTIN	4046356801690
Weight per piece (including packing)	4,480 g
Weight per piece (excluding packing)	4,470 g
Customs tariff number	85176200
Country of origin	TW

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch



2891079

<https://www.phoenixcontact.com/gb/products/2891079>

## Technical data

### Dimensions

Width	442 mm
Height	44 mm
Depth	375 mm

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

### Mounting

Mounting type	Rack mount, includes brackets
---------------	-------------------------------

### Interfaces

#### Ethernet (RJ45)

Connection method	RJ45
Note on the connection method	Auto negotiation and autocrossing
Transmission speed	10/100 Mbps
Transmission physics	Ethernet in RJ45 twisted pair
Transmission length	100 m
No. of channels	8 (RJ45 ports)

#### Fiber optic interface

Connection method	SC
Transmission speed	100 Mbps (Full duplex)
Transmission physics	multi-mode fiberglass
Transmission length	8 km (fiberglass with F-G 62.5/125 0.7 dB/km F1000) 3.3 km (fiberglass with F-G 62.5/125 2.6 dB/km F600) 9.6 km (fiberglass with F-G 50/125 0.7 dB/km F1200) 5.3 km (fiberglass with F-G 50/125 1.6 dB/km F800)
Wavelength	1300/1310 nm
No. of channels	16 (Multi mode)

#### Ethernet (RJ45/FO combo)

Connection method	SFP/RJ45
Note on the connection method	Auto negotiation and autocrossing (RJ45 interface)
Transmission speed	10/100/1000 Mbps
Transmission physics	Ethernet RJ45 (10/100/1000 Mbps) or SFP (1000 Mbps)
No. of channels	4 (Combo ports)

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch



2891079

<https://www.phoenixcontact.com/gb/products/2891079>

## Product properties

Product type	Switch
Product family	Managed Switch 4000
Type	Block design
MTTF	7.3 Years (MIL-HDBK-217F standard, temperature 25°C, operating cycle 100%) 41.2 Years (SN 29500 standard, temperature 25°C, operating cycle 21%) 19.8 Years (Telcordia standard, 25°C temperature, 21% operating cycle (5 days a week, 8 hours a day))

## Switch functions

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
Redundancy	ERR (Extended ring redundancy)
Status and diagnostic indicators	LEDs: U <sub>S1</sub> , U <sub>S2</sub> (redundant voltage supply), link and activity per port

## Security functions

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
-----------------	--

## Electrical properties

Transmission medium	Copper FO
---------------------	--------------

## Supply

Power supply connection	From FL SWITCH 4800E-P...
-------------------------	---------------------------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)
Air pressure (operation)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)
Air pressure (storage/transport)	57 kPa ... 108 kPa (up to 4850 m above mean sea level)

## Standards and regulations

Standard designation	Ambient conditions
Standards/specifications	IEC 61850-3

## EMC data

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch



2891079

<https://www.phoenixcontact.com/gb/products/2891079>

Noise immunity	IEC 61850-3, IEEE 1613, EN 61000-6-2: 2005
Noise emission	EN 61000-6-4

## System properties

### Functionality

Basic functions	Store and forward switch, Extended Ring and IEEE redundancy, Multicast control, IGMP snooping, trunking, Port and Tagging VLANs, Port and IEEE 802.1x security, SNMP V3 and Https security, SNTP, web customization, user accounts
-----------------	--

## Signaling

Status display	LEDs: $U_{S1}$ , $U_{S2}$ (redundant voltage supply), link and activity per port
----------------	--

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch




2891079

<https://www.phoenixcontact.com/gb/products/2891079>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/gb/products/2891079>

 **UL Listed**  
Approval ID: E140403

 **cUL Listed**  
Approval ID: E140403

 **KC**  
Approval ID: MSIP-REI-PCK-2891079

**cULus Listed**

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch



2891079

<https://www.phoenixcontact.com/gb/products/2891079>

## Classifications

### ECLASS

ECLASS-11.0	19170401
ECLASS-12.0	19170401
ECLASS-13.0	19170401

### ETIM

ETIM 9.0	EC000734
----------	----------

### UNSPSC

UNSPSC 21.0	43222600
-------------	----------

# FL SWITCH 4808E-16FX-4GC - Industrial Ethernet Switch



2891079

<https://www.phoenixcontact.com/gb/products/2891079>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	15(a), 6(c), 7(a), 7(c)-I

### China RoHS

Environment friendly use period (EFUP)	EFUP-10
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
SCIP	f74063f7-d6e1-4acd-9061-ecca83a5faae

Phoenix Contact 2025 © - all rights reserved

<https://www.phoenixcontact.com>

PHOENIX CONTACT Ltd  
Halesfield 13, Telford  
Shropshire, TF7 4PG  
01952 681700  
[info@phoenixcontact.co.uk](mailto:info@phoenixcontact.co.uk)