

# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP30-rated fanless industrial box PC (BPC) with energy-efficient Intel® Celeron® N3350 processor with 32 GB eMMC mass storage, 64 GB M.2 SSD, 2x COM ports, Windows 10 Enterprise 2019 LTSC operating system, Wi-Fi, and a Trusted Platform Module (TPM)

## Commercial data

|                                      |               |
|--------------------------------------|---------------|
| Item number                          | 1158244       |
| Packing unit                         | 1 pc          |
| Sales key                            | DR12          |
| Product key                          | DRBABA        |
| GTIN                                 | 4063151163938 |
| Weight per piece (including packing) | 920 g         |
| Weight per piece (excluding packing) | 650 g         |
| Customs tariff number                | 84715000      |
| Country of origin                    | TW            |

1158244

<https://www.phoenixcontact.com/us/products/1158244>

## Technical data

### Product properties

|              |        |
|--------------|--------|
| Product type | Box PC |
|--------------|--------|

### Computer data

|                     |   |
|---------------------|---|
| Processor           | Intel® Celeron® N3350 1.10/2.4 GHz                            |
| Operating system    | Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language |
| Cooling             | passive   |
| RAM                 | 4 GB LPDDR4   |
| Data storage system | eMMC internal, 32 GB<br>64 GB M.2 SSD                         |

### Display

|              |      |
|--------------|------|
| Display type | none |
|--------------|------|

### System properties

|               |                       |
|---------------|-----------------------|
| User software | without user software |
|---------------|-----------------------|

### Electrical properties

|   |        |
|---|--------|
| Maximum power dissipation for nominal condition | 16.8 W |
|---|--------|

### Supply

|                             |   |
|-----------------------------|---|
| Supply voltage (DC)         | 24 V DC (CE rating)   |
| Supply voltage range        | 12 V DC ... 30 V DC (Labeled operational voltage is 12 ... 30 V DC) |
| Max. current consumption    | 0.7 A (24 V DC)   |
| Typical current consumption | 0.53 A (24 V DC)  |

### Connection data

#### Screw connection

|                                   |   |
|-----------------------------------|---|
| Connection method                 | Screw connection                            |
| Conductor cross section, rigid    | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section, flexible | 0.2 mm <sup>2</sup> ... 2.5 mm <sup>2</sup> |
| Conductor cross section AWG       | 25 ... 14                                   |

### Interfaces

|             |                                      |
|-------------|--------------------------------------|
| Interfaces  | 1x DP++                              |
|             | 2x USB 3.0                           |
|             | 2x COM ports                         |
|             | 1x Wireless LAN                      |
| Network     | 2x Ethernet (10/100/1000 Mbps), RJ45 |
| LAN chipset | Intel® I210-AT                       |

### Dimensions

1158244

<https://www.phoenixcontact.com/us/products/1158244>

## External dimensions

|                        |                       |
|------------------------|-----------------------|
| Width / Height / Depth | 99 mm / 92 mm / 63 mm |
|------------------------|-----------------------|

## Environmental and real-life conditions

### Ambient conditions

|   |  |
|---|--|
| Degree of protection                    | IP30   |
|   | IP30   |
| Ambient temperature (operation)         | -20 °C ... 50 °C (with 0.5 m/s airflow)      |
| Ambient temperature (storage/transport) | -40 °C ... 85 °C                             |
| Permissible humidity (operation)        | 5 % ... 85 % (non-condensing)                |
| Shock                                   | 15g, 11 ms in accordance with IEC 60068-2-27 |
| Vibration (operation)                   | 1g, according to EN 60068-2-6                |

## Approvals

### Conformity/Approvals

|             |   |
|-------------|---|
| Conformance | CE-compliant                            |
| FCC         | Title 47 Part 15 Subpart B:2018 Class A |

## Mounting

|               |                                      |
|---------------|--------------------------------------|
| Mounting type | DIN rail mounting                    |
|               | Wall mounting (Accessories required) |

# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

## Approvals

🔗 To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1158244>



**EAC**

Approval ID: RU C-DE.A\*08.B01708



**EAC-RoHS**

Approval ID: RU\*-DE\*HB.B.00386/20

# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

## Classifications

### ECLASS

|             |          |
|-------------|----------|
| ECLASS-11.0 | 19200102 |
| ECLASS-12.0 | 19200102 |
| ECLASS-13.0 | 19200102 |

### ETIM

|          |          |
|----------|----------|
| ETIM 9.0 | EC001413 |
|----------|----------|

### UNSPSC

|             |          |
|-------------|----------|
| UNSPSC 21.0 | 43211500 |
|-------------|----------|

# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

## Environmental product compliance

REACH SVHC

Lead 7439-92-1

# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

## Accessories

### SI-RND-U1A - Data interface

1425185

<https://www.phoenixcontact.com/us/products/1425185>

Service socket with USB A 3.0 (socket/socket), with protective cover



---

### DP TO VGA ADPTR - Adapter

2400173

<https://www.phoenixcontact.com/us/products/2400173>

DisplayPort to VGA video adapter



# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

## DP TO DVI ADPTR - Adapter

2400174

<https://www.phoenixcontact.com/us/products/2400174>

DisplayPort to DVI-i video adapter



---

## VL 2.0M DP CABLE - Connecting cable

2404774

<https://www.phoenixcontact.com/us/products/2404774>

DisplayPort (DP) cable (2 m) for use with industrial computers





## BL2 BPC 1501E-W-64-W10-T - Box PC

1158244

<https://www.phoenixcontact.com/us/products/1158244>



## BL2 BPC 1500 WALL MOUNT KIT - Mounting kit

1147655

<https://www.phoenixcontact.com/us/products/1147655>

Mounting kit



---

## BL2 BPC 1500 RTC BATTERY - Battery/accumulator

1147739

<https://www.phoenixcontact.com/us/products/1147739>

Replacement battery (BR2030) for BL2 BPC 1500... IPCs



# BL2 BPC 1501E-W-64-W10-T - Box PC



1158244

<https://www.phoenixcontact.com/us/products/1158244>

## BL2 BPC 1500 DIN RAIL KIT - Mounting kit

1147464

<https://www.phoenixcontact.com/us/products/1147464>



DIN rail mounting kit for BL2 BPC 15... products

---

## BL2 BPC 1500 64GB M.2 SSD KIT - Memory

1147738

<https://www.phoenixcontact.com/us/products/1147738>



64 GB M.2 SSD kit for BL2 1500 IPC, heat spreader, bracket, and thermal pads are included

## BL2 BPC 1501E-W-64-W10-T - Box PC

1158244

<https://www.phoenixcontact.com/us/products/1158244>



### BL2 BPC 1500 128GB M.2 SSD KIT - Memory

1147737

<https://www.phoenixcontact.com/us/products/1147737>



128 GB M.2 SSD kit for BL2 1500 IPC, heat spreader, bracket, and thermal pads are included

---

### BL2 X100 480GB 2.5 SSD MLC - Memory

1185762

<https://www.phoenixcontact.com/us/products/1185762>



480 GB 2.5 SSD kit for BL2 x100 IPCs

# BL2 BPC 1501E-W-64-W10-T - Box PC




1158244

<https://www.phoenixcontact.com/us/products/1158244>

## MC 1,5/ 2-STF-3,5 - PCB connector

1847055

<https://www.phoenixcontact.com/us/products/1847055>



PCB connector, nominal cross section: 1.5 mm<sup>2</sup>, color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: MC 1,5/...-STF, pitch: 3.5 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)