

SACB-16X0,34/2X0,75-50 PUR - Master cable ring



1539350

<https://www.phoenixcontact.com/us/products/1539350>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Master cable for sensor/actuator boxes, without PE conductor, unshielded, material PUR/PVC, 18-pos., 16 x 0.34 mm² and 2 x 0.75 mm², length: 50 m



Commercial data

Item number	1539350
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BF45
Product key	BF3ZBX
Catalog page	Page 305 (C-2-2019)
GTIN	4046356077767
Weight per piece (including packing)	7,100 g
Weight per piece (excluding packing)	7,100 g
Customs tariff number	85444995
Country of origin	DE

SACB-16X0,34/2X0,75-50 PUR - Master cable ring



1539350

<https://www.phoenixcontact.com/us/products/1539350>

Technical data

Product properties

Product type	Cable by the meter
Number of positions	18
Application	Distributor boxes
LED	No

Electrical properties

Nominal voltage U_N	300 V AC
	300 V DC

Cable/line

Cable length	50 m
--------------	------

PUR/PVC black [PUR]

Number of positions	18
Shielded	no
Cable type	PUR/PVC black [PUR]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	16x 0.34 mm ² (Signal line)
	2x 0.75 mm ² (Power supply)
External cable diameter	10.1 mm ±0.2 mm
Outer sheath, material	PUR
External sheath, color	deep black RAL 9005
Conductor material	Bare Cu litz wires
Material wire insulation	PVC
Single wire, color	brown, blue, white, green, yellow, gray, pink, red, black, violet, gray/pink, red/blue, white/green, brown/green, white/yellow, yellow/brown, white/gray, gray/brown
Overall twist	Wires twisted in layers
Nominal voltage, cable	300 V (Signal line)
	500 V (Power supply)
Test voltage	1200 V (Signal line)
	2000 V (Power supply)
Max. bending cycles	1500000
Flame resistance	DIN EN 50265
Resistance to oil	according to VDE 0472 Part 803
Other resistance	Highly resistant to acids, alkaline solutions and solvents
Special properties	Silicone-free
Ambient temperature (operation)	-40 °C ... 90 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SACB-16X0,34/2X0,75-50 PUR - Master cable ring



1539350

<https://www.phoenixcontact.com/us/products/1539350>

Classifications

ECLASS

ECLASS-11.0	27060106
ECLASS-12.0	27060106
ECLASS-13.0	27060106

ETIM

ETIM 9.0	EC003250
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SACB-16X0,34/2X0,75-50 PUR - Master cable ring



1539350

<https://www.phoenixcontact.com/us/products/1539350>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

SACB-16X0,34/2X0,75-50 PUR - Master cable ring



1539350

<https://www.phoenixcontact.com/us/products/1539350>

Accessories

WIREFOX-D 13 - Stripping tool

1212162

<https://www.phoenixcontact.com/us/products/1212162>



Stripping tool, for stripping installation lines of \varnothing 8 - 13 mm , e.g. NYM 3 x 1.5 mm² to 5 x 2.5 mm², single line stripping 0.2 mm² - 4 mm² , with longitudinal cut blade and sliding knife

WIREFOX-D 40 - Stripping tool

1212161

<https://www.phoenixcontact.com/us/products/1212161>



Stripping tool, for stripping cables of 4.5 mm - 40 mm- \varnothing , insulation thickness of up to 4.5 mm, pivoting blade for round, lengthwise, and spiral cuts

SACB-16X0,34/2X0,75-50 PUR - Master cable ring



1539350

<https://www.phoenixcontact.com/us/products/1539350>

WIREFOX 4 - Stripping tool

1212156

<https://www.phoenixcontact.com/us/products/1212156>



Stripping tool, for cables and conductors (especially for rubber and silicone insulations) from 0.1 - 4 mm², self-adjusting, stripping length of up to 18 mm, cutting capacity of up to 10 mm² stranded/1.5 mm² solid, replaceable stripping blade

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com