

SAC-3P-100,0-100/0,34 - Cable reel



1502206

<https://www.phoenixcontact.com/us/products/1502206>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



By the meter, Cable reel, PUR halogen-free, gray RAL 7001, color single wire: brown, blue, black, cable length: 100 m

Commercial data

Item number	1502206
Packing unit	1 pc
Minimum order quantity	1 pc
Note	Made to order (non-returnable)
Sales key	BF11
Product key	BF1LBA
GTIN	4017918811594
Weight per piece (including packing)	2,190 g
Weight per piece (excluding packing)	2,190 g
Customs tariff number	85444290
Country of origin	DE

SAC-3P-100,0-100/0,34 - Cable reel

1502206

<https://www.phoenixcontact.com/us/products/1502206>

Technical data

Product properties


Number of positions	3
---------------------	---

Cable/line

Cable length	100 m
--------------	-------

PUR halogen-free gray [280]

Dimensional drawing



Cable weight	23.42 kg/km
UL AWM Style	20549 / 10493 (80°C/300 V)
Shielded	no
Cable type	PUR halogen-free gray [280]
Conductor structure signal line	42x 0.10 mm
AWG signal line	22
Conductor cross section	3x 0.34 mm ² (Signal line)
Wire diameter incl. insulation	1.27 mm ±0.05 mm
External cable diameter	3.95 mm ±0.15 mm
Outer sheath, material	PUR
External sheath, color	gray RAL 7001
Conductor material	Bare Cu litz wires
Material wire insulation	PP
Single wire, color	brown, blue, black
Thickness, insulation	≥ 0.203 mm
Thickness, outer sheath	approx. 0.4 mm
Overall twist	3 wires, twisted
Max. conductor resistance	≤ 58 Ω/km
Insulation resistance	≥ 20 MΩ*km
Nominal voltage, cable	≤ 300 V
Test voltage	≥ 3000 V
Minimum bending radius, fixed installation	5 x D
Minimum bending radius, flexible installation	10 x D
Max. bending cycles	10000000
Halogen-free	in accordance with DIN VDE 0472 part 815 EN 50267-2-1

SAC-3P-100,0-100/0,34 - Cable reel



1502206

<https://www.phoenixcontact.com/us/products/1502206>

Flame resistance	in accordance with UL 758/1581 FT2
	DIN EN 60332-2-2 (20 s)
Resistance to oil	in accordance with DIN EN 60811-2-1
Other resistance	Highly resistant to acids, alkaline solutions and solvents
	hydrolysis and microbe resistant
	partly UV-resistant in accordance with DIN EN ISO 4892-2-A
	Low adhesion
Special properties	abrasion-resistant
	Flexible cable conduit capable
	Silicone-free
	Free of substances which would hinder coating with paint or varnish
Ambient temperature (operation)	flexible
	-40 °C ... 80 °C (cable, fixed installation)
	-25 °C ... 80 °C (Cable, flexible installation)

Environmental and real-life conditions

Ambient conditions

Ambient temperature (operation)	-25 °C ... 80 °C (cable, fixed installation)
	-5 °C ... 80 °C (Cable, flexible installation)

SAC-3P-100,0-100/0,34 - Cable reel



1502206

<https://www.phoenixcontact.com/us/products/1502206>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1502206>



EAC-RoHS

Approval ID: RU D-DE.HB35.B.00371

SAC-3P-100,0-100/0,34 - Cable reel



1502206

<https://www.phoenixcontact.com/us/products/1502206>

Classifications

ECLASS

ECLASS-11.0	27061801
ECLASS-12.0	27061801
ECLASS-13.0	27061801

ETIM

ETIM 9.0	EC003249
----------	----------

UNSPSC

UNSPSC 21.0	26121600
-------------	----------

SAC-3P-100,0-100/0,34 - Cable reel



1502206

<https://www.phoenixcontact.com/us/products/1502206>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

SAC-3P-100,0-100/0,34 - Cable reel



1502206

<https://www.phoenixcontact.com/us/products/1502206>

Accessories

WIREFOX SAC - Stripping tool

1212623

<https://www.phoenixcontact.com/us/products/1212623>



Stripping pliers, for halogen-free sensor/actuator cables (SAC cables), with PUR and PVC insulation, from Ø of 4.4 to 7 mm, any stripping length

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com