

WT-HF 3,6X140 - Cable tie

3240744

<https://www.phoenixcontact.com/us/products/3240744>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Cable binders for quick and secure bundling, standard version

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 3240744 |
| Packing unit | 1 pc |
| Minimum order quantity | 100 pc |
| Sales key | BE07 |
| Product key | BE7131 |
| Catalog page | Page 614 (C-3-2019) |
| GTIN | 4046356704601 |
| Weight per piece (including packing) | 0.675 g |
| Weight per piece (excluding packing) | 0.67 g |
| Customs tariff number | 39269097 |
| Country of origin | IT |

WT-HF 3,6X140 - Cable tie



3240744

<https://www.phoenixcontact.com/us/products/3240744>

Technical data

Product properties

| | |
|----------------------|----------------|
| Product type | Cable tie |
| Type | Internal teeth |
| Tensile strength GRP | 130 N |

Dimensions

| | |
|--------|--------|
| Width | 3.6 mm |
| Length | 140 mm |

Material specifications

| | |
|--|--------------------------------|
| Color | transparent |
| Material | PA 6.6 |
| Flammability rating according to UL 94 | V2 |
| Components | free from silicone and halogen |

Cable/line

| | |
|-------------------------|----------------|
| External cable diameter | 2 mm ... 35 mm |
| Tensile strength | 130 N |

Environmental and real-life conditions

Ambient conditions

| | |
|---|---|
| Optimum ambient temperature (storage/transport) | 23 °C 50 % Polyamide 6.6 has pronounced hygroscopic properties. It absorbs or releases water in accordance with the level of humidity within its environment. Its properties are ideal when the percentage of water is 2 - 3%. The packaging, which is tailored specifically to the product concerned, contains the optimum level of moisture. To ensure that the ideal properties are maintained, the following points should be observed during storage: Keep product stored inside sealed original packaging, carry out any product processing soon after breaking open the packaging, avoid direct sunlight, avoid direct heat. |
| Ambient temperature (operation) | -40 °C ... 85 °C |
| Ambient temperature (assembly) | -10 °C ... 60 °C |
| Resistance to UV radiation | no |
| Short-term temperature | 110 °C |

Standards and regulations

| | |
|----------------------------|----|
| Resistance to UV radiation | no |
|----------------------------|----|

Mounting

| | |
|---------------|-------------------|
| Mounting type | Cannot be removed |
|---------------|-------------------|

WT-HF 3,6X140 - Cable tie

3240744

<https://www.phoenixcontact.com/us/products/3240744>



Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/3240744>



UL Recognized



LR

WT-HF 3,6X140 - Cable tie

3240744

<https://www.phoenixcontact.com/us/products/3240744>



Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-11.0 | 27140702 |
| ECLASS-12.0 | 27140702 |
| ECLASS-13.0 | 27140702 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC000046 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 39121700 |
|-------------|----------|

WT-HF 3,6X140 - Cable tie

3240744

<https://www.phoenixcontact.com/us/products/3240744>



Environmental product compliance

| | |
|------------|---|
| China RoHS | Environmentally friendly use period: unlimited = EFUP-e |
| | No hazardous substances above threshold values |

WT-HF 3,6X140 - Cable tie

3240744

<https://www.phoenixcontact.com/us/products/3240744>



Accessories

UNIFOX-CT 4,8 - Cable tie tool

1212475

<https://www.phoenixcontact.com/us/products/1212475>



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

UNIFOX-CT 4,8P - Cable tie tool

1212609

<https://www.phoenixcontact.com/us/products/1212609>



Cable binder pliers, for plastic cable binders with a width of 2.2 - 4.8 mm, for a material thickness of up to 1.6 mm

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com