

MM-EML (EX24)R C1 TR/BK - Label



1116133

<https://www.phoenixcontact.com/us/products/1116133>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Label, Roll, transparent/black, unlabeled, can be labeled with: THERMOMARK GO, THERMOMARK GO.K, THERMOFOX, mounting type: adhesive, lettering field size: continuous x 22 mm

Product description

The MM-EML... polyester self-adhesive labels are available as continuous media for equipment marking.

Your advantages

- The material is cUL certified
- High-quality and solvent-resistant marking solution for industrial applications that is created by means of thermal transfer printing
- The self-adhesive material in continuous format is particularly suitable for the professional and permanent marking of various components and equipment in control cabinet, controller, and systems manufacturing
- Easy and efficient material cartridge system: Includes both the material to be printed and the corresponding ink ribbon
- Thanks to the continuous format, a label of the appropriate length can be created flexibly for the relevant application

Commercial data

Item number	1116133
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	BG23
Product key	BG241E
GTIN	4063151040888
Weight per piece (including packing)	73 g
Weight per piece (excluding packing)	60 g
Customs tariff number	96121010
Country of origin	CN

Technical data

Product properties

Product type	Device marking
--------------	----------------

Marking

Identification technology	Thermal transfer
---------------------------	------------------

Mounting

Mounting type	adhesive
---------------	----------

Material specifications

RoHS compliant	yes
Adhesive	Acrylic
Color	transparent/black
Material	Polyester
Components	free from silicone, halogen, and cadmium

Environmental and real-life conditions

Test for substances that would hinder coating with paint or varnish

Result	Test passed
--------	-------------

UV resistance

Specification	ISO 4892-2:2013-03 (following)
Result	Test passed
Test duration	96 h

Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-1):2011-07
	DIN EN 62208 (VDE 0660-511):2012-06 (in parts)

Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	DIN 50018:2013-05
Result	Test passed
Climate level	AHT 1.0 S
Cycles	2

Salt spray test

Specification	DIN EN 60068-2-11:2000-02
Result	Test passed

Ambient conditions

Ambient temperature (operation)	-40 °C ... 150 °C
Recommended storage conditions	23 °C/50 % relative humidity. Storage in a dry and dark place in the original packaging is recommended.
Recommended ambient temperature (storage/transport)	23 °C

MM-EML (EX24)R C1 TR/BK - Label



1116133

<https://www.phoenixcontact.com/us/products/1116133>

Recommended humidity (storage/transport)	50 %
Shelf life	12 months

Dimensions

Width	24 mm
Length	8 m

Standards and regulations

Wipe resistance	DIN EN 61010-1 (VDE 0411-1)
-----------------	-----------------------------

MM-EML (EX24)R C1 TR/BK - Label



1116133

<https://www.phoenixcontact.com/us/products/1116133>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1116133>



cULus Recognized
Approval ID: MH48542

MM-EML (EX24)R C1 TR/BK - Label



1116133

<https://www.phoenixcontact.com/us/products/1116133>

Classifications

ECLASS

ECLASS-11.0	27281103
ECLASS-12.0	27281103
ECLASS-13.0	27281103

ETIM

ETIM 9.0	EC001288
----------	----------

UNSPSC

UNSPSC 21.0	39131500
-------------	----------

MM-EML (EX24)R C1 TR/BK - Label



1116133

<https://www.phoenixcontact.com/us/products/1116133>

Environmental product compliance

China RoHS	Environmentally friendly use period: unlimited = EFUP-e
	No hazardous substances above threshold values

MM-EML (EX24)R C1 TR/BK - Label



1116133

<https://www.phoenixcontact.com/us/products/1116133>

Accessories

THERMOMARK GO - Thermal transfer printer

1090747

<https://www.phoenixcontact.com/us/products/1090747>



Mobile thermal transfer printer for marking materials in cartridge format incl. accessories. The printer can print prepunched labels as well as materials in continuous format up to a material width of 24 mm

THERMOMARK GO.K - Thermal transfer printer

1184146

<https://www.phoenixcontact.com/us/products/1184146>



Mobile thermal transfer printer for marking materials in cartridge format. The printer can print materials in continuous format up to a material width of 24 mm.

MM-EML (EX24)R C1 TR/BK - Label

1116133

<https://www.phoenixcontact.com/us/products/1116133>



THERMOFOX - Thermal transfer printer

0803984

<https://www.phoenixcontact.com/us/products/0803984>



Portable thermal transfer printer for roll material

THERMOFOX CN - Thermal transfer printer

0803985

<https://www.phoenixcontact.com/us/products/0803985>



Portable thermal transfer printer for materials off the roll, version with Chinese firmware and Chinese keypad

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com