

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



CHARX connect, Cooling unit, Accessories, with variable-speed fan, with variable-speed pump, for cooling the cooling liquid of a Phoenix Contact HPC DC charging cable, HPC CCS type 2, HPC CCS type 1, length: 1.5 m

Commercial data

Item number	1237881
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	EM01
Product key	XWBALL
GTIN	4063151344757
Weight per piece (including packing)	17,440 g
Weight per piece (excluding packing)	17,440 g
Customs tariff number	84195080
Country of origin	DE

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Technical data

Product properties

Product type	Cooling unit
Product family	CHARX connect
Application	for cooling the cooling liquid of a Phoenix Contact HPC DC charging cable for installation in e-mobility charging stations (EVSE)
Type	Accessories
Design	with variable-speed fan with variable-speed pump
Manufacturer	HYDAC Cooling GmbH
Technology	High Power Charging Combined Charging System
Charging standard	HPC CCS type 2 HPC CCS type 1
Charging mode	Mode 4

Electrical properties

Supply voltage	24 V DC (Fan) 24 V DC (Pump)
Control voltage range	0 V DC ... 10 V DC (Fan) 0 V DC ... 10 V DC (Pump)
Current consumption	max. 1.97 A (Fan) max. 1.8 A (Pump)

Interfaces

Function interface: Cooling system

Interface description	Quick release couplings, inflow and return flow, for hoses with an outer diameter of 12 mm
-----------------------	--

Function interface: Fan

Cable structure	4 x 0.5 mm ²
Single-core wire	Power supply RD Reference ground BU Speed output WH Control input YE

Function interface: Pump

Cable structure	2 x 0.34 mm ² + 5 x 0.14 mm ²
Single-core wire	Power supply RD Reference ground BK Motor shutoff signal GN Speed output BN

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

	Control input YE
	RS-485 Modbus WH can only be used by the manufacturer
	RS-485 Modbus BU can only be used by the manufacturer

Function interface: Level sensor

connection	Plug straight M12 A
------------	---------------------

Material specifications

Material (Housing)	Aluminum
	Stainless steel

Cable/line

Cable length	1.5 m (Fan)
	1.5 m (Pump)
Cable length	1.5 m (Fan)
Cable length	1.5 m (Pump)

Mechanical properties

Cooling capacity	approx. 0.06 kW/K (at 2 l/min)
Volumetric flow	approx. 2 l/min (at 1 □bar)
Coolant	50% water, 50% glycol (Glysofor N)

Environmental and real-life conditions

Ambient conditions

Degree of protection (Fans)	IP55 (Fan)
Degree of protection (Pump)	IP65 (Pump)
Ambient temperature (operation)	-20 °C ... 50 °C
Ambient temperature (storage/transport)	-25 °C ... 50 °C
Altitude	max. 1000 m (above sea level)
Volume	≤ 60 db(A) (with free-standing system and 1 m distance)

EV-HPC-PCU-01 - Cooling unit


1237881

<https://www.phoenixcontact.com/us/products/1237881>



Drawings

Schematic diagram



Coolant tank fill-level sensor connected via M12 male with A-coding

EV-HPC-PCU-01 - Cooling unit



1237881

<https://www.phoenixcontact.com/us/products/1237881>

Classifications

ECLASS

ECLASS-11.0	27144792
ECLASS-12.0	27144792
ECLASS-13.0	27144792

ETIM

ETIM 9.0	EC002884
----------	----------

UNSPSC

UNSPSC 21.0	39121500
-------------	----------

EV-HPC-PCU-01 - Cooling unit

1237881

<https://www.phoenixcontact.com/us/products/1237881>



Environmental product compliance

REACH SVHC	Lead 7439-92-1
	Lead titanium zirconium oxide 12626-81-2

EV-HPC-PCU-01 - Cooling unit

1237881

<https://www.phoenixcontact.com/us/products/1237881>



Accessories

EV-T2HPCC-DC500A-5,0M50ECBK11 - DC charging cable

1085638

<https://www.phoenixcontact.com/us/products/1085638>



CHARX connect professional, HPC DC charging cable, with cooled vehicle charging connector and cooled cable, for charging electric vehicles (EV) with direct current (DC), with replaceable mating face frame, with replaceable DC power contacts, without panel feed-through, with digital temperature sensors, HPC CCS type 2, IEC 62196-3-1, 500 A / 1000 V (DC), PHOENIX CONTACT logo, cable: 5 m, black, straight

EV-T1HPCC-DC500A-5,0M50ECBK11 - DC charging cable

1085658

<https://www.phoenixcontact.com/us/products/1085658>



CHARX connect professional, HPC DC charging cable, with cooled vehicle charging connector and cooled cable, for charging electric vehicles (EV) with direct current (DC), with charging connector holder, with replaceable mating face frame, without panel feed-through, with digital temperature sensors, HPC CCS type 1, SAE J1772, IEC 62196-3-1, 500 A / 1000 V (DC), PHOENIX CONTACT logo, cable: 5 m, black, straight

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA

586 Fulling Mill Road

Middletown, PA 17057, United States

(+717) 944-1300

info@phoenixcon.com