

VS-09-DSUB-20-LI-5,0 - D-SUB cable



1656259

<https://www.phoenixcontact.com/us/products/1656259>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Assembled D-SUB cable, shielded, 9-pos., stranded (7-wire), cable color: RAL 7000 (gray), secured using 4-40 UNC thread, IP20 protection, head 1 with socket shell 1 and straight cable outlet, head 2 with pin shell 1 and straight cable outlet, length: 5 m

Commercial data

| | |
|--------------------------------------|---------------------|
| Item number | 1656259 |
| Packing unit | 1 pc |
| Minimum order quantity | 1 pc |
| Sales key | AB19 |
| Product key | ABNCAS |
| Catalog page | Page 218 (C-2-2013) |
| GTIN | 4046356029735 |
| Weight per piece (including packing) | 231 g |
| Weight per piece (excluding packing) | 223.5 g |
| Customs tariff number | 85444290 |
| Country of origin | CN |

VS-09-DSUB-20-LI-5,0 - D-SUB cable



1656259

<https://www.phoenixcontact.com/us/products/1656259>

Technical data

Product properties

| | |
|---------------------|-------------------------|
| Product type | Data cable preassembled |
| Type | D-SUB |
| Sensor type | Universal |
| Number of positions | 9 |
| Cable outlet | straight |

Data management status

| | |
|------------------|----|
| Article revision | 03 |
|------------------|----|

Insulation characteristics

| | |
|----------------------|-----|
| Overvoltage category | III |
| Degree of pollution | 2 |

Electrical properties

| | |
|---------------------|--------|
| Rated current | 1 A |
| Operating voltage | 30 V |
| Transmission medium | Copper |

Mechanical properties

Mechanical data

| | |
|-----------------------------|------|
| Insertion/withdrawal cycles | ≥ 50 |
|-----------------------------|------|

Material specifications

| | |
|--------------------------|--------------|
| Housing material | PVC |
| Contact material | Copper alloy |
| Contact surface material | gold-plated |
| Outer sheath, material | PVC |

Connection data

Connection technology

| | |
|-------------------|-------|
| Connection method | D-SUB |
|-------------------|-------|

Conductor connection

| | |
|-------------------|-------|
| Connection method | D-SUB |
|-------------------|-------|

Connector

Connection 1

| | |
|------|-------------------------|
| Type | Socket straight D-SUB 9 |
|------|-------------------------|

Connection 2

| | |
|------|-----------------------|
| Type | Plug straight D-SUB 9 |
|------|-----------------------|

VS-09-DSUB-20-LI-5,0 - D-SUB cable



1656259

<https://www.phoenixcontact.com/us/products/1656259>

Cable/line

| | |
|------------------------|----------------------|
| Outer sheath, material | PVC |
| Cable cross section | 0.08 mm ² |
| AWG signal line | 28 |

Environmental and real-life conditions

Ambient conditions

| | |
|---------------------------------|----------------|
| Degree of protection | IP20 |
| | IP20 |
| Ambient temperature (operation) | 0 °C ... 70 °C |


VS-09-DSUB-20-LI-5,0 - D-SUB cable

1656259


<https://www.phoenixcontact.com/us/products/1656259>

Drawings

Schematic diagram



Circuit diagram




VS-09-DSUB-20-LI-5,0 - D-SUB cable

1656259

<https://www.phoenixcontact.com/us/products/1656259>



Schematic diagram



Connector pin assignment

VS-09-DSUB-20-LI-5,0 - D-SUB cable



1656259

<https://www.phoenixcontact.com/us/products/1656259>

Classifications

ECLASS

| | |
|-------------|----------|
| ECLASS-12.0 | 27060390 |
| ECLASS-11.0 | 27060390 |
| ECLASS-13.0 | 27060307 |

ETIM

| | |
|----------|----------|
| ETIM 9.0 | EC001855 |
|----------|----------|

UNSPSC

| | |
|-------------|----------|
| UNSPSC 21.0 | 26121600 |
|-------------|----------|

VS-09-DSUB-20-LI-5,0 - D-SUB cable



1656259

<https://www.phoenixcontact.com/us/products/1656259>

Environmental product compliance

EU RoHS

| | |
|---|--------------------|
| Fulfills EU RoHS substance requirements | Yes, No exemptions |
|---|--------------------|

China RoHS

| | |
|--|--|
| Environment friendly use period (EFUP) | EFUP-E |
| | No hazardous substances above the limits |

EU REACH SVHC

| | |
|-------------------------------------|----------------------------|
| REACH candidate substance (CAS No.) | No substance above 0.1 wt% |
|-------------------------------------|----------------------------|

Phoenix Contact 2024 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com