

# TM-PTRV 8,QR:H-A - Marker for terminal blocks



0803473

<https://www.phoenixcontact.com/us/products/0803473>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Marker for terminal blocks, Strip, white (RAL 9010), labeled, mounting type: latching, for terminal block width: 8 mm, Number of individual labels: 2, text field height: 9.2 mm, text field width: 2.4 mm

## Commercial data

Item number	0803473
Packing unit	10 pc
Minimum order quantity	10 pc
Sales key	BG05
Product key	BG2122
GTIN	4055626074535
Weight per piece (including packing)	1.41 g
Weight per piece (excluding packing)	1.35 g
Customs tariff number	49119900
Country of origin	PL

## Technical data

### Product properties

Product type	Terminal marker
Pitch	8 mm

### Marking

Number of individual labels	2
Number of individual labels per row	4
Slot type	high

### Dimensions

Width	2.40 mm
Height	44.19 mm
Depth	73.85 mm
Pitch	8 mm

### Text field

Text field width	2.4 mm
Text field height	9.2 mm

### Material specifications

Color	white (RAL 9010)
Flammability rating according to UL 94	V2
Base element material	PA

### Environmental and real-life conditions

#### Ambient conditions

Ambient temperature (operation)	100 °C
Recommended ambient temperature (storage/transport)	23 °C
Recommended humidity (storage/transport)	50 % (Storage in a dry and dark place in the original packaging is recommended)

#### Test for substances that would hinder coating with paint or varnish

Testing for paint wetting impairment substances (LABS-conformity)	VDMA 24364:2018-05
Result	Test passed

#### Scratch resistance

Specification	EN ISO 1518-1:2023 (following)
Requirements	≥ 5 N
Result	Test passed

#### Tesafilm test

Specification	DIN EN ISO 2409:2020-12 (following)
Result	Test passed

# TM-PTRV 8,QR:H-A - Marker for terminal blocks



0803473

<https://www.phoenixcontact.com/us/products/0803473>

## UV resistance

Specification	DIN EN ISO 4892-2:2021-11 (following)
Result	Test passed
Test duration	96 h
Procedure	Artificial irradiation.

## Temperature resistance

Specification	ANSI/UL 969-2018:03 (following)
Test duration	240 h
Rating 100 °C (121 °C)	Test passed

## Wipe resistance of inscriptions

Specification	DIN EN 61010-1 (VDE 0411-01):2020-03 DIN EN 62208 (VDE 0660-511):2012-06 (in parts)
Isopropanol (99%) [67-63-0]	Test passed
n-Hexane [CAS No. 110-54-3]	Test passed
Water + Petroleum ether [CAS No. 64742-82-1]	Test passed
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Ethanol (99 %) [CAS No. 64-17-5]	Test passed

## Immersion in chemicals, oil & fuel

Specification	ISO 175:2010 (following)
Test duration	168 h
Sodium hydroxide 0.1 mol/l [CAS No. 1310-73-2]	Test passed
Saltwater (saturated 350 g/l) [CAS No. - ]	Test passed
Gasoline [CAS No. 64742-49-0]	Test passed
Diesel [CAS No. 68476-34-6]	Test passed
IRM 901	Test passed
IRM 902	Test passed
IRM 903	Test passed

## Testing in a condensation changing climate in the presence of sulfur dioxide

Specification	EN ISO 22479:2022-06
Result	Test passed
Procedure	Method B
Cycles	2

## Salt spray test

Specification	DIN EN IEC 60068-2-11 (VDE 0468-2-11):2022-10
Result	Test passed

# TM-PTRV 8,QR:H-A - Marker for terminal blocks



0803473

<https://www.phoenixcontact.com/us/products/0803473>

Test duration	96 h
---------------	------

## Mounting

Mounting type	latching
---------------	----------

# TM-PTRV 8,QR:H-A - Marker for terminal blocks



0803473

<https://www.phoenixcontact.com/us/products/0803473>

## Classifications

### ECLASS

ECLASS-13.0	27281101
ECLASS-15.0	27281101

### ETIM

ETIM 10.0	EC000761
-----------	----------

### UNSPSC

UNSPSC 21.0	39131500
-------------	----------

# TM-PTRV 8,QR:H-A - Marker for terminal blocks



0803473

<https://www.phoenixcontact.com/us/products/0803473>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2026 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)