

HS LCA-RGB-10X5-L - Signal light

1082299

<https://www.phoenixcontact.com/us/products/1082299>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



10 mm signal light with SMD-LED 5 mm (color: RGB) for assembly on wall thicknesses from 1.5 mm. Black housing made of polycarbonate (UL 94-V0) with four 94 mm tin-plated free wire ends, watertight IP68 (EN 60529)

Commercial data

Item number	1082299
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	AC05
Product key	ACGABC
GTIN	4055626812632
Weight per piece (including packing)	6.7 g
Weight per piece (excluding packing)	1.035 g
Customs tariff number	85318070
Country of origin	TN

HS LCA-RGB-10X5-L - Signal light



1082299

<https://www.phoenixcontact.com/us/products/1082299>

Technical data

Notes

General	Refer to the data sheet for the range in the download area.
---------	-------------------------------------------------------------

Product properties

Product type	Light
Number of positions	1
Alignment	flexible
Type	active, flexible
Conductor type	Signal light with litz wires
Head form	Raised head
Number of indicators	1 (1 row x 1 column)

Dimensions

Diameter	10 mm (Aperture diameter)
	5 mm (Lens diameter)
Hole diameter	8 mm
Dimensions	94 mm (Cable ends)

Material specifications

Color Linse	transparent
Color Gehäuse	black (9005)
Insulating material	PC

Environmental and real-life conditions

Ambient conditions

Max. IP code to attain	IP68
Ambient temperature (operation)	-20 °C ... 80 °C

Packaging specifications

Type of packaging	PE bag
-------------------	--------

HS LCA-RGB-10X5-L - Signal light



1082299

<https://www.phoenixcontact.com/us/products/1082299>

Classifications

ECLASS

ECLASS-11.0	27110201
ECLASS-13.0	27110350
ECLASS-12.0	27110350

ETIM

ETIM 9.0	EC002750
----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

HS LCA-RGB-10X5-L - Signal light

1082299

<https://www.phoenixcontact.com/us/products/1082299>



Environmental product compliance

China RoHS

Environmentally friendly use period: unlimited = EFUP-e

No hazardous substances above threshold values

HS LCA-RGB-10X5-L - Signal light



1082299

<https://www.phoenixcontact.com/us/products/1082299>

Accessories

SZS 0,4X2,0 - Screwdriver

1205202

<https://www.phoenixcontact.com/us/products/1205202>



Micro screwdriver, bladed, size: 0.4 x 2.0 x 60 mm, 2-component grip, with non-slip grip and twist cap

PTSM 0,5/ 4-PL-2,5 WH - Printed-circuit board connector

1709460

<https://www.phoenixcontact.com/us/products/1709460>



PCB connector, nominal cross section: 0.5 mm², color: white, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: PTSM 0,5/...-PL WH, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON PTSM, locking: Snap-in locking, mounting: Self-locking flange, type of packaging: packed in cardboard

HS LCA-RGB-10X5-L - Signal light

1082299

<https://www.phoenixcontact.com/us/products/1082299>



PTSM 0,5/ 4-PL-2,5 BK - Printed-circuit board connector

1709444

<https://www.phoenixcontact.com/us/products/1709444>



PCB connector, nominal cross section: 0.5 mm², color: black, nominal current: 6 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 4, number of rows: 1, number of positions: 4, number of connections: 4, product range: PTSM 0,5/...-PL, pitch: 2.5 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON PTSM, locking: Snap-in locking, mounting: Self-locking flange, type of packaging: packed in cardboard

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com