

BL2 PPC10 1201-4/128-W10 - Panel PC



1274014

<https://www.phoenixcontact.com/us/products/1274014>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



IP65 panel PC (PPC) with 10-inch screen, Intel® Celeron® N3350 processor, 4 GB of RAM, 128 GB mSATA SSD, and Windows 10 IoT Enterprise LTSC 2019 operating system.

Commercial data

Item number	1274014
Packing unit	1 pc
Sales key	DR12
Product key	DRBABB
GTIN	4063151466039
Weight per piece (including packing)	2,530 g
Weight per piece (excluding packing)	1,900 g
Customs tariff number	84714100
Country of origin	TW

1274014

<https://www.phoenixcontact.com/us/products/1274014>

Technical data

Product properties

Product type	Panel PC
--------------	----------

Computer data

Processor	Intel® Celeron® N3350
Operating system	Windows® 10 IoT Enterprise LTSC 2019 (64-bit), Multi-language
Cooling	passive
RAM	4 GB DDR3 SODIMM
Data storage system	128 GB mSATA

Display

Display type	25.7 cm / 10.1" TFT
Screen resolution	1024 x 600 Pixel(s) (WVGA)
Touch technology	projective-capacitive (PCAP)
Display lighting type	LED
Brightness	300 cd/m ² , typical (adjustable)
MTBF	> 25000 h
Color spectrum	262000 colors
Reading angle bottom	10-point touch

System properties

User software	without user software
---------------	-----------------------

Electrical properties

Service life of battery	5 years (typical)
-------------------------	-------------------

Supply

Power supply unit	24 V DC ±20 %
Max. current consumption	1.09 A

Real-time clock

Realtime clock	Yes (battery-backed)
----------------	----------------------

Connection data

Connection method	Screw connection
Conductor cross section, rigid	0.14 mm ² ... 1.5 mm ²
Conductor cross section, flexible	0.14 mm ² ... 1.5 mm ²
Conductor cross section AWG	28 ... 16
Stripping length	7 mm

Interfaces

Interfaces	1x COM (RS-232)
	1x USB 2.0
	2x USB 3.0

BL2 PPC10 1201-4/128-W10 - Panel PC



1274014

<https://www.phoenixcontact.com/us/products/1274014>

	2x COM (RS-232/422/485)
Monitor output	1x HDMI
Network	2x Ethernet (10/100/1000 Mbps), RJ45
LAN chipset	Intel® I210-AT

Dimensions

External dimensions

Width / Height / Depth	266 mm / 184 mm / 48 mm
------------------------	-------------------------

Installation dimensions

Width / Height / Installation depth	229 mm / 155 mm / (Panel cutout for 10" display)
-------------------------------------	--

Environmental and real-life conditions

Ambient conditions

Degree of protection	IP65 (front), IP20 (back)
Ambient temperature (operation)	-5 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 70 °C
Permissible humidity (operation)	10 % ... 90 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 90 % (non-condensing)
Shock	20g, 11 ms in accordance with IEC 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

Mounting

Mounting type	Front mounting
	VESA holder (not for industrial use)
Holder system	VESA MIS-D 75
	VESA MIS-D 100 C

BL2 PPC10 1201-4/128-W10 - Panel PC



1274014

<https://www.phoenixcontact.com/us/products/1274014>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1274014>



EAC

Approval ID: RU C-DE.A*08.B01708



UL Listed

Approval ID: FILE E 238705



cUL Listed

Approval ID: FILE E 238705



EAC-RoHS

Approval ID: RU*-DE*HB.B.00386/20

cULus Listed

BL2 PPC10 1201-4/128-W10 - Panel PC



1274014

<https://www.phoenixcontact.com/us/products/1274014>

Classifications

ECLASS

ECLASS-11.0	19200103
ECLASS-12.0	19200103
ECLASS-13.0	19200103

ETIM

ETIM 9.0	EC001414
----------	----------

UNSPSC

UNSPSC 21.0	43211500
-------------	----------

1274014

<https://www.phoenixcontact.com/us/products/1274014>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
	1,2-dimethoxyethane,ethylene glycol dimethyl ether (EGDME) 110-71-4
	Lead titanium trioxide 12060-00-3
China RoHS	Environmentally Friendly Use Period = 10;
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

BL2 PPC10 1201-4/128-W10 - Panel PC



1274014

<https://www.phoenixcontact.com/us/products/1274014>

Accessories

VISU+ IPC UPGRADE - Visualization software

1310994

<https://www.phoenixcontact.com/us/products/1310994>




Visu+ IPC UPGRADE product is a made-to-order upgrade to the Visu+ HMI runtime that was originally ordered with your Phoenix Contact IPC system.

MC 1,5/ 2-STF-3,81 - PCB connector

1827703

<https://www.phoenixcontact.com/us/products/1827703>



PCB connector, nominal cross section: 1.5 mm², color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: MC 1,5/..-STF, pitch: 3.81 mm, connection method: Screw connection with tension sleeve, screw head form: L Slotted, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

BL2 PPC10 1201-4/128-W10 - Panel PC



1274014

<https://www.phoenixcontact.com/us/products/1274014>

FMC 1,5/ 2-STF-3,81 - Printed-circuit board connector

1748354

<https://www.phoenixcontact.com/us/products/1748354>



PCB connector, nominal cross section: 1.5 mm², color: green, nominal current: 8 A, rated voltage (III/2): 160 V, contact surface: Tin, contact connection type: Socket, number of potentials: 2, number of rows: 1, number of positions: 2, number of connections: 2, product range: FMC 1,5/..-STF, pitch: 3.81 mm, connection method: Push-in spring connection, conductor/PCB connection direction: 0 °, plug-in system: COMBICON MC 1,5, locking: Screw locking mechanism, mounting: Screw flange, type of packaging: packed in cardboard

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com