

# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Axioline P, Digital output module, Digital output: 4, 24 V DC, connection technology: 2-conductor, Solenoid drive, Intrinsically safe, transmission speed in the local bus: 100 Mbps, degree of protection: IP20, including bus base module and connectors

## Product description

The module is an Axioline P I/O module for use in the Axioline P modular I/O system. The module is a modular I/O device that can be affixed to the Axioline P local bus, to communicate I/O data up to the Axioline P bus coupler, which forms the head of the station. As an intrinsic safety I/O module, this device allows direct connection from intrinsically safe field I/O to the terminals of the module. The module is fully hot-swappable on the Axioline P local bus, which also provides power to the module. The module digital output characteristics of 24 V DC and 48 mA allow the connection of up to four solenoid driven, digital output signals.

## Your advantages

- Four 24 V DC - 48 mA digital output-powered control signals for solenoid drives
- Intrinsically safe digital outputs with connection to Zone 1, Zone 0 or Division 1
- Temperature range: -40 °C ... +70 °C
- Hot-swappable

## Commercial data

Item number	1087077
Packing unit	1 pc
Sales key	NULL
Product key	DRIP32
GTIN	4055626882192
Weight per piece (including packing)	385.5 g
Weight per piece (excluding packing)	266.4 g
Customs tariff number	85389099
Country of origin	US

# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Technical data

### Dimensions

Dimensional drawing	
Width	53.6 mm
Height	126.1 mm
Depth	77.14 mm
Note on dimensions	The depth applies when a TH 35-7.5 DIN rail is used (in accordance with EN 60715).

### Notes

#### Utilization restriction

EMC note	EMC: class A product, see manufacturer's declaration in the download area
----------	---

#### Utilization restriction

CCCex note	Use in potentially explosive areas is not permitted in China.
------------	---

### Material specifications

Color	traffic grey A RAL 7042
-------	-------------------------

### Interfaces

#### Axioline P local bus

Connection method	Connection for bus base module
Transmission speed	100 Mbps

### Output data

#### Digital

Output name	Digital output
Connection method	Push-in connection
Connection technology	2-conductor
Number of outputs	4
Protective circuit	Polarity reversal protection of the outputs
Output voltage	24 V
Maximum output current per channel	48 mA
Nominal output voltage	24 V DC

### Product properties

# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

Type	block modular
Product type	I/O component
Product family	Axioline P
Mounting position	any (no temperature derating)
Scope of delivery	including bus base module and connectors

## Insulation characteristics

Overvoltage category	II
Pollution degree	2

## Electrical properties

### Potentials: Supply of the logic voltage $U_L$

Supply voltage range	19.2 V DC ... 30 V DC (via bus base module ( $U_L$ ) at AXL P BK...)
----------------------	--

### Potentials: Supply of the Axioline P local bus $U_{BUS}$

Supply voltage	5 V DC (via bus base module)
Current draw	max. 135 mA

### Potentials: Axioline P extension module supply voltage

Supply voltage	$U_L$ (via bus base module)
Current draw	max. 455 mA (via bus base module)

### Electrical isolation/isolation of the voltage ranges

Test voltage: 5 V supply of the local bus ( $U_{BUS}$ ) / functional ground	500 V AC, 62 Hz, 1 min.
Test voltage: 24 V supply (I/O) / functional ground	500 V AC, 62 Hz, 1 min.
Test voltage: Field to functional earth	500 V AC, 62 Hz, 1 min.
Test voltage: Field to 5 V and 24 V supplies	1500 V AC, 62 Hz, 1 min.

## Connection data

### Connection technology

Connection name	Axioline P connector
Note on the connection method	Please observe the information provided on conductor cross sections in the "Axioline P: system and installation" user manual.

### Conductor connection

Connection method	Push-in connection
Conductor cross section rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section flexible	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>
Conductor cross section AWG	24 ... 16
Stripping length	8 mm

### Axioline P connector

Connection method	Push-in connection
Note on the connection method	Please observe the information provided on conductor cross sections in the "Axioline P: system and installation" user manual.
Conductor cross section, rigid	0.2 mm <sup>2</sup> ... 1.5 mm <sup>2</sup>

1087077

<https://www.phoenixcontact.com/us/products/1087077>

Conductor cross section, flexible	0.2 mm² ... 1.5 mm²
Conductor cross section AWG	24 ... 16
Stripping length	8 mm

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-40 °C ... 70 °C (Standard)
Degree of protection	IP20
Air pressure (operation)	70 kPa ... 106 kPa (up to 2000 m above sea level)
Air pressure (storage/transport)	70 kPa ... 106 kPa (up to 2000 m above sea level)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Permissible humidity (operation)	5 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	5 % ... 95 % (non-condensing)

## Standards and regulations

Protection class	III (IEC 61140, EN 61140, VDE 0140-1)
------------------	---------------------------------------

## Approvals

### ATEX

Identification	II 3(1) G Ex ec [ia Ga] IIC T4 Gc II (1) D [Ex ia Da] IIIC
Certificate	DEMKO 20 ATEX 2370X

### IECEX

Identification	Ex ec [ia Ga] IIC T4 Gc [Ex ia Da] IIIC
Certificate	IECEX UL 20.0044X

### UKCA Ex (UKEX)

Identification	II 3(1) G Ex ec [ia Ga] IIC T4 Gc II (1) D [Ex ia Da] IIIC
Certificate	UL22UKEX2508X

### Ex data

UL, USA / Canada	Ind. Cont. Eq. (E238705) also Listed Ind. Cont. Eq. for haz. loc. E196811 Install in: Class I, Div. 2, Groups A, B, C, D T4 Intrinsically safe outputs for: Class I, Groups A, B, C, D; Class II, Groups E, F, G; Class III; [Ex ia] Haz loc Class I, Zone 2, AEx ec [ia Ga] IIC T4 Gc [AEx ia Da] IIIC Ex ec [ia Ga] IIC T4 Gc [Ex ia Da] IIIC
------------------	--

## Mounting

Mounting type	DIN rail mounting
Mounting position	any (no temperature derating)

# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Ex data

### Safety data

Max. output voltage $U_o$	27.3 V
Max. output current $I_o$	99 mA
Max. output power $P_o$	676 mW
Safety-related maximum voltage $U_m$	250 V
A, B / IIC ((A, B, or IIC)): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	/ 0.088 $\mu$ F
C/IIB, IIIC ((C, IIB, or IIIC)): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	/ 0.683 $\mu$ F
D/IIA, E, F, G, Class III ((D, E, F, G, Class III, or IIA)): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	/ 2.28 $\mu$ F
A, B / IIC ((A, B, or IIC)): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	1.189 mH
C/IIB, IIIC ((C, IIB, or IIIC)): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	12.9 mH
D/IIA, E, F, G, Class III ((D, E, F, G, Class III, or IIA)): Max. external inductivity $L_o$ / Max. external capacitance $C_o$	27.41 mH

# AXL P EX IS DO4 SD 24-48 1F - Digital module




1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Drawings

Dimensional drawing



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1087077>



**UL Listed**

Approval ID: FILE E 238705



**cUL Listed**

Approval ID: FILE E 238705



**IECEX**

Approval ID: IECEX UL 20.0044X



**CCC**

Approval ID: 2021122316114727



**cUL Listed**

Approval ID: FILE E 196811



**UL Listed**

Approval ID: FILE E 196811



**ATEX**

Approval ID: DEMKO 20 ATEX 2370X

**cULus Listed**

**cULus Listed**

# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Classifications

### ECLASS

ECLASS-11.0	27242604
ECLASS-12.0	27242604
ECLASS-13.0	27242604

### ETIM

ETIM 9.0	EC001599
----------	----------

### UNSPSC

UNSPSC 21.0	32151600
-------------	----------



# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Environmental product compliance

REACH SVHC	Lead 7439-92-1
	Dechlorane Plus
China RoHS	Environmentally Friendly Use Period = 25;
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## Accessories

### AXL P BS F2 - Bus connector

1052428

<https://www.phoenixcontact.com/us/products/1052428>




Axioline P bus base module for housing type F2

---

### AXL SHIELD SET - Shield connection

2700518

<https://www.phoenixcontact.com/us/products/2700518>



Axioline shield connection set (contains 2 shield bus holders and 2 SK 5 shield connection clamps)

# AXL P EX IS DO4 SD 24-48 1F - Digital module

1087077

<https://www.phoenixcontact.com/us/products/1087077>



## AXL F/P IO EX PP - Separating plate

1100201

<https://www.phoenixcontact.com/us/products/1100201>

Axioline F/P partition plate for intrinsically safe modules



---

## AXL P TERM PAIR - Termination block

2316402

<https://www.phoenixcontact.com/us/products/2316402>

Axioline P terminator pair



# AXL P EX IS DO4 SD 24-48 1F - Digital module



1087077

<https://www.phoenixcontact.com/us/products/1087077>

## ZB 20,3 AXL UNPRINTED - Zack marker strip

0829579

<https://www.phoenixcontact.com/us/products/0829579>



Zack marker strip for Axioline F (device labeling), in 2 x 20.3 mm pitch, unprinted, 25-section, for individual labeling with B-STIFT 0.8, X-PEN, or CMS-P1-PLOTTER

---

## AXL P TERM PAIR - Termination block

2316402

<https://www.phoenixcontact.com/us/products/2316402>



Axioline P terminator pair

# AXL P EX IS DO4 SD 24-48 1F - Digital module

1087077

<https://www.phoenixcontact.com/us/products/1087077>



## AXL P BS F2 - Bus connector

1052428

<https://www.phoenixcontact.com/us/products/1052428>

Axioline P bus base module for housing type F2



---

Phoenix Contact 2023 © - all rights reserved

<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)