

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Redundancy module, 5 ... 24 V DC, 2x 5 A, 1x 10 A



Product description

A safe redundant system is the result of the parallel connection of two power supply units which are decoupled from one another. To further increase system availability, STEP DIODE provides the solution: decoupling with diode.

Your advantages

- Flexible mounting by simply snapping onto the DIN rail
- Save energy
- Rugged design
- Permanent monitoring of redundancy
- Consistent redundancy up to the load

Commercial data

Item number	2868606
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	CM18
Product key	CMRS43
Catalog page	Page 309 (C-4-2019)
GTIN	4046356583923
Weight per piece (including packing)	78.238 g
Weight per piece (excluding packing)	73 g
Customs tariff number	85049090
Country of origin	VN

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Technical data

Input data

DC operation

Nominal input voltage range	5 V DC ... 24 V DC
Input voltage range	4.5 V DC ... 30 V DC
Voltage type of supply voltage	DC
Reverse polarity protection	< yes60 V
Nominal input current (I_N)	2x 5 A (-25 °C ... 55 °C)
	1x 10 A (-25 °C ... 55 °C)
	2x 5 A (-25 °C ... 55 °C)
	1x 10 A (-25 °C ... 55 °C)
Transient surge protection	Transil diode
Voltage drop, input/output	0.5 V

Output data

Efficiency	> 97 %
	> 97 %
Nominal output voltage	24 V DC
Output voltage	U_{In} -
Setting range of the output voltage (U_{Set})	5 V DC ... 24 V DC
Nominal output current (I_N)	10 A (Increasing power)
	5 A (Redundancy)
Derating	55 °C ... 70 °C (2.5%/K)
Power loss nominal load max.	2.5 W ($I_{OUT} = 5$ A)
Connection in series	No
Derating	60 °C ... 70 °C (2.5%/K)

Connection data

Input

Connection method	Screw connection
Conductor cross section, rigid min.	0.2 mm ²
Conductor cross section, rigid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	6.5 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

Output

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Connection method	Screw connection
Conductor cross section, rigid min.	0.2 mm ²
Conductor cross section, rigid max.	2.5 mm ²
Conductor cross section flexible min.	0.2 mm ²
Conductor cross section flexible max.	2.5 mm ²
Conductor cross section AWG min.	24
Conductor cross section AWG max.	12
Stripping length	6.5 mm
Screw thread	M3
Tightening torque, min	0.5 Nm
Tightening torque max	0.6 Nm

Electrical properties

Insulation voltage input, output / housing	500 V DC
--	----------

Product properties

Product type	Redundancy module
Product family	STEP DIODE
MTBF (IEC 61709, SN 29500)	> 25822000 h (40 °C)
LED	No

Insulation characteristics

Protection class	III
Degree of pollution	2

Dimensions

Width	18 mm
Height	90 mm
Depth	61 mm
Horizontal pitch	1 Div.

Installation dimensions

Installation distance right/left	0 mm / 0 mm
Installation distance top/bottom	30 mm / 30 mm

Mounting

Mounting type	DIN rail: 35 mm
Assembly instructions	alignable: 0 mm horizontally, 30 mm vertically
Mounting position	horizontal DIN rail NS 35, EN 60715

Material specifications

Housing material	Metal
Housing material	Plastic

Environmental and real-life conditions

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Ambient conditions

Degree of protection	IP20
Ambient temperature (operation)	-25 °C ... 70 °C (> 55° C derating : 2.5%/K)
Ambient temperature (storage/transport)	-40 °C ... 85 °C
Climatic class	3K3 (in acc. with EN 60721)
Max. permissible relative humidity (operation)	≤ 95 % (at 25 °C, non-condensing)
Shock	18 ms, 30g, in each space direction (according to IEC 60068-2-27)
Vibration (operation)	< 15 Hz, amplitude ±2.5 mm (according to IEC 60068-2-6) 15 Hz ... 150 Hz, 2.3g, 90 min.

Standards and regulations

Standard – Electronic equipment for use in electrical power installations and their assembly into electrical power installations	EN 50178/VDE 0160 (PELV)
Standard - Electrical safety	IEC 62368-1 (SELV)

Approvals

UL approvals	UL/C-UL listed UL 508 UL/C-UL Recognized UL 60950-1
--------------	--

EMC data

Low Voltage Directive	Conformance with Low Voltage Directive 2014/35/EC
EMC requirements for noise emission	EN 61000-6-3 EN 61000-6-4
EMC requirements for noise immunity	EN 61000-6-1 EN 61000-6-2
Electromagnetic compatibility	Conformance with EMC Directive 2014/30/EU

Electrostatic discharge

Standards/regulations	EN 61000-4-2
-----------------------	--------------

Electrostatic discharge

Contact discharge	4 kV (Test Level 2)
Discharge in air	8 kV (Test Level 3)
Comments	Criterion B

Electromagnetic HF field

Standards/regulations	EN 61000-4-3
-----------------------	--------------

Electromagnetic HF field

Frequency range	80 MHz ... 1 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	1 GHz ... 2 GHz
Test field strength	10 V/m (Test Level 3)
Frequency range	2 GHz ... 3 GHz
Test field strength	10 V/m (Test Level 3)

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Comments	Criterion A
Fast transients (burst)	
Standards/regulations	EN 61000-4-4
Fast transients (burst)	
Input	2 kV (Test Level 3 - asymmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
Comments	Criterion B
Surge voltage load (surge)	
Standards/regulations	EN 61000-4-5
Input	2 kV (Test Level 3 - asymmetrical)
	1 kV (Test Level 2 - symmetrical)
Output	2 kV (Test Level 3 - asymmetrical)
	1 kV (Test Level 2 - symmetrical)
Comments	Criterion B
Conducted interference	
Standards/regulations	EN 61000-4-6
Conducted interference	
I/O/S	asymmetrical
Frequency range	150 kHz ... 80 MHz
Comments	Criterion A
Voltage	10 V (Test Level 3)
Voltage dips	
Standards/regulations	EN 61000-4-11
Emitted interference	
Standards/regulations	EN 61000-6-3
Radio interference voltage in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Emitted radio interference in acc. with EN 55011	EN 55011 (EN 55022) Class B, area of application: Industry and residential
Criteria	
Criterion A	Normal operating behavior within the specified limits.
Criterion B	Temporary impairment to operational behavior that is corrected by the device itself.

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module




2868606

<https://www.phoenixcontact.com/us/products/2868606>

Drawings

Block diagram



STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/2868606>



cUL Recognized
Approval ID: FILE E 214596



UL Recognized
Approval ID: FILE E 214596



EAC
Approval ID: EAC-Zulassung



EAC
Approval ID: EAC-Zulassung



UL Listed
Approval ID: FILE E 123528



cUL Listed
Approval ID: FILE E 123528



UL Recognized
Approval ID: FILE E 214596



cUL Recognized
Approval ID: FILE E 214596



cUL Listed
Approval ID: FILE E 123528



UL Listed
Approval ID: FILE E 123528



EAC
Approval ID: RU S-DE.BL08.W.00764

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>



EAC

Approval ID: RU S-DE.BL08.W.00764

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Classifications

ECLASS

ECLASS-11.0	27371010
ECLASS-12.0	27371010
ECLASS-13.0	27371010

ETIM

ETIM 9.0	EC000683
----------	----------

UNSPSC

UNSPSC 21.0	32151500
-------------	----------

STEP-DIODE/5-24DC/2X5/1X10 - Redundancy module



2868606

<https://www.phoenixcontact.com/us/products/2868606>

Environmental product compliance

REACH SVHC	Lead 7439-92-1
China RoHS	Environmentally Friendly Use Period = 25;
	For information on hazardous substances, refer to the manufacturer's declaration available under "Downloads"

Phoenix Contact 2023 © - all rights reserved
<https://www.phoenixcontact.com>

Phoenix Contact USA
586 Fulling Mill Road
Middletown, PA 17057, United States
(+717) 944-1300
info@phoenixcon.com