

# UTA 130 - DIN rail adapter



2706412

<https://www.phoenixcontact.com/us/products/2706412>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.

Universal DIN rail adapter for screwing on switchgear



## Commercial data

Item number	2706412
Packing unit	5 pc
Minimum order quantity	1 pc
Sales key	AC07
Product key	ACGEAD
Catalog page	Page 764 (C-1-2013)
GTIN	4017918822743
Weight per piece (including packing)	147.7 g
Weight per piece (excluding packing)	146.7 g
Customs tariff number	79070000
Country of origin	DE

# UTA 130 - DIN rail adapter



2706412

<https://www.phoenixcontact.com/us/products/2706412>

## Technical data

### Product properties

Product type	DIN rail adapter
Housing type	DIN rail adapter
Product family	UTA
Type	Fastening holes provided, integrated foot catch

### Data management status

Article revision	00
------------------	----

### Dimensions

Width	52 mm
Height	130 mm
Depth	9.6 mm

### Material specifications

Housing material	Zinc die-cast
------------------	---------------

### Environmental and real-life conditions

#### Vibration test

Specification	IEC 60068-2-6:2007-12
Frequency	10 - 150 - 10 Hz
Sweep speed	1 octave/min
Amplitude	0.35 mm (10 Hz ... 60.1 Hz)
Acceleration	5g (60.1 Hz ... 150 Hz)
Test duration per axis	2.5 h
Test directions	X-, Y- and Z-axis

### Mounting

Mounting type	DIN rail mounting
---------------	-------------------

# UTA 130 - DIN rail adapter

2706412

<https://www.phoenixcontact.com/us/products/2706412>



## Classifications

### ECLASS

ECLASS-11.0	27370419
ECLASS-12.0	27370419
ECLASS-13.0	27370419

### ETIM

ETIM 9.0	EC001024
----------	----------

### UNSPSC

UNSPSC 21.0	39121400
-------------	----------

# UTA 130 - DIN rail adapter



2706412

<https://www.phoenixcontact.com/us/products/2706412>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes, No exemptions
---	--------------------

### China RoHS

Environment friendly use period (EFUP)	EFUP-E
	No hazardous substances above the limits

### EU REACH SVHC

REACH candidate substance (CAS No.)	No substance above 0.1 wt%
-------------------------------------	----------------------------

Phoenix Contact 2024 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)