

# BTP 2070W - Touch panel



1046666

<https://www.phoenixcontact.com/us/products/1046666>

Please be informed that the data shown in this PDF document is generated from our online catalog. Please find the complete data in the user documentation. Our general terms of use for downloads are valid.



Touch panel with 17.8 cm / 7"-TFT display (analog resistive), 800 x 480 pixel(s) (WVGA), 16.7 million colors, Arm® Cortex®-A7, 528 MHz i.MX6 UL, 2x COM (RS-232/422/485), 1x USB 2.0, Typ A, 1x USB 2.0, Typ B, 1 x Ethernet (10/100 Mbps), RJ45, Windows® Embedded Compact 7 and user software: Visu+. (bus system: without)

## Your advantages

- Visu+ RT integrated as standard in all BTP 2000 devices
- Connection to all relevant control systems, thanks to a large number of available drivers
- Developed for basic applications with attractive price/performance ratio
- 3 display sizes in 16:9 format

## Commercial data

Item number	1046666
Packing unit	1 pc
Minimum order quantity	1 pc
Sales key	DR17
Product key	DRCEBC
Catalog page	Page 471 (C-6-2019)
GTIN	4055626642963
Weight per piece (including packing)	688.5 g
Weight per piece (excluding packing)	400 g
Customs tariff number	84714100
Country of origin	IN

# BTP 2070W - Touch panel



1046666

<https://www.phoenixcontact.com/us/products/1046666>

## Technical data

### Notes

#### Note on application

Note on application	Only for industrial use
---------------------	-------------------------

### Product properties

Product type	Operator panel
--------------	----------------

#### Computer data

Processor	Arm® Cortex®-A7, 528 MHz i.MX6 UL
Operating system	Windows® Embedded Compact 7
RAM	512 MB DDR3 SDRAM
Data storage system	eMMC, 4 GB
Slots	1x SD

#### Display

Display type	17.8 cm / 7"-TFT
Screen resolution	800 x 480 Pixel(s) (WVGA)
Touch technology	analog resistive
Display lighting type	LED
Brightness	350 cd/m <sup>2</sup> , typical (adjustable)
MTBF	25000 h
Color spectrum	16.7 million colors
Reading angle left	70.00 °
Reading angle right	70.00 °
Reading angle top	50.00 °
Reading angle bottom	70.00 °

### Interfaces

Interfaces	2x COM (RS-232/422/485)
	1x USB 2.0, Typ A
	1x USB 2.0, Typ B
Network	1 x Ethernet (10/100 Mbps), RJ45
Bus system	without

### System properties

User software	Visu+
---------------	-------

### Electrical properties

#### Supply

Power supply unit	24 V DC ±15 %
Typical current consumption	0.4 A

# BTP 2070W - Touch panel



1046666

<https://www.phoenixcontact.com/us/products/1046666>

## Mounting

Mounting type	Front mounting
---------------	----------------

## Material specifications

Housing material	Plastic
------------------	---------

## Environmental and real-life conditions

### Ambient conditions

Degree of protection	IP66 (front), IP20 (back)
Ambient temperature (operation)	0 °C ... 50 °C
Ambient temperature (storage/transport)	-20 °C ... 85 °C
Permissible humidity (operation)	10 % ... 95 % (non-condensing)
Permissible humidity (storage/transport)	10 % ... 95 % (non-condensing)
Shock	DIN EN 60068-2-27
Vibration (operation)	DIN EN 60068-2-6

## Dimensions

### External dimensions

Width / Height / Depth	186 mm / 138 mm / 5 mm (Dimensions of the front plate)
------------------------	--

### Installation dimensions

Width / Height / Installation depth	175 mm / 127 mm / 31 mm (Installation cutout)
-------------------------------------	---

# BTP 2070W - Touch panel



1046666

<https://www.phoenixcontact.com/us/products/1046666>

## Approvals

To download certificates, visit the product detail page: <https://www.phoenixcontact.com/us/products/1046666>



**cUL Listed**

Approval ID: E196811



**UL Listed**

Approval ID: FILE E 196811



**UL Listed**

Approval ID: FILE E 196811



**cUL Listed**

Approval ID: E196811

# BTP 2070W - Touch panel

1046666

<https://www.phoenixcontact.com/us/products/1046666>



## Classifications

### ECLASS

ECLASS-11.0	27330201
ECLASS-12.0	27330201
ECLASS-13.0	27330201

### ETIM

ETIM 9.0	EC001412
----------	----------

### UNSPSC

UNSPSC 21.0	43211900
-------------	----------

# BTP 2070W - Touch panel



1046666

<https://www.phoenixcontact.com/us/products/1046666>

## Environmental product compliance

### EU RoHS

Fulfills EU RoHS substance requirements	Yes
Exemption	7(a)

### China RoHS

Environment friendly use period (EFUP)	EFUP-50
	An article-related China RoHS declaration table can be found in the download area for the respective article under "Manufacturer declaration". For all articles with EFUP-E, no China RoHS declaration table issued and required.

### EU REACH SVHC

REACH candidate substance (CAS No.)	Lead(CAS: 7439-92-1)
-------------------------------------	----------------------

Phoenix Contact 2025 © - all rights reserved  
<https://www.phoenixcontact.com>

Phoenix Contact USA  
586 Fulling Mill Road  
Middletown, PA 17057, United States  
(+717) 944-1300  
[info@phoenixcon.com](mailto:info@phoenixcon.com)